




PANDUIT PART NUMBER	FIBER TYPE	FIBER COUNT	MAX IL (dB)	MIN RL (dB)
FXTLSLSE5EAAMLLL	50/125OM3	12	0.50	30
FZTSLSE5EAAMLLL	50/125 OM4			
FXUSLSE5EAAMLLL	50/125 OM3	24	0.50	30
FZUSLSE5EAAMLLL	50/125 OM4			

- NOTES:
1. MAXIMUM INSERTION LOSS IS 0.35 dB PER CONNECTOR.
 2. CONNECTOR MEETS THE REQUIREMENTS OF TIA-568-C.3.
 3. MPO POLARITY COMPLIES WITH METHOD "A" PER TIA-568-C.0
 4. LSZH-RATED CABLE ASSEMBLIES MEET IEC-60332, IEC-60754 AND IEC-61034 REQUIREMENTS.
 5. CABLE MEETS THE MECHANICAL REQUIREMENTS OF ICEA-S-83-596 AND TELCORDIA GR-409-CORE.
 6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
 7. MAXIMUM STRENGTH OF THE PULLING EYE IS 20 lbs.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01	10-15-15	SAT	JSP	EJH	A. UPDATED CABLE DIA.	12F178BG-DCA
R	03-11-13	SAT	WMA		RELEASED FOR CUSTOMER APPROVAL	12F178BG-DCA

PART NUMBER	SEE TABLE 1	PRODUCT SPEC/REV SPEC	N/A
L.I. NUMBER	N/A	WORK IDENTIFICATION	N/A
TITLE	12 & 24 FIBER MPO TO MPO LSZH TRUNK CABLE WITH PULLING EYE		
ITEM REVISION NAME	CUSTOMER APPROVAL DRAWING		
DATASET FILE NAME	12F178BG/01	PANDUIT	
	12F178BG_DCA/01A		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (IN 1 mm)			
.xx ± .12, .54		.xxx ± .005 (.127)	
.xx ± .01 (.25)		ANGLES ± 5°	
THIRD ANGLE PROJECTION	DRAWING NUMBER: 12F178BG-DCA		
DRAWN BY	DATE	CHK	SCALE
SAT	03-11-13	WMA	NONE
SHT 1 OF 1			D