




TABLE 1				
PANDUIT PART NUMBER	FIBER TYPE	FIBER COUNT	MAX IL (dB)	MIN RL (dB)
FXTLSLSE5EAAMLLL	50/125OM3	12	0.50	30
FZTSLSE5EAAMLLL	50/125 OM4			
FXUSLSE5EAAMLLL	50/125 OM3	24	0.50	30
FZUSLSE5EAAMLLL	50/125 OM4			

- NOTES:
1. MAXIMUM INSERTION LOSS IS 0.35 dB PER CONNECTOR.
 2. CONNECTOR MEETS THE REQUIREMENTS OF TIA-568-C.3.
 3. MPO POLARITY COMPLIES WITH METHOD "A" PER TIA-568-C.0
 4. LSZH-RATED CABLE ASSEMBLIES MEET IEC-60332, IEC-60754 AND IEC-61034 REQUIREMENTS.
 5. CABLE MEETS THE MECHANICAL REQUIREMENTS OF ICEA-S-83-596 AND TELCORDIA GR-409-CORE.
 6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
 7. MAXIMUM STRENGTH OF THE PULLING EYE IS 20 lbs.



PART NUMBER		SEE TABLE 1		PRODUCT SPEC/MS SPEC		N/A	
I.T.I. NUMBER		N/A		WORK INSTRUCTIONS		N/A	
TITLE 12 & 24 FIBER MPO TO MPO LSZH TRUNK CABLE WITH PULLING EYE CUSTOMER APPROVAL DRAWING							
ITEM REVISION NAME 12F178BG/01				DATE			
DATASET FILE NAME 12F178BG_DCA/01A				PANDUIT			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (IN 1 mm) xx +.12, .541 -xxx +.005 (.127) xx +.01 (.254) ANGLES ± 5°							
DI	10-15-15	SAT	JSP	EJH	A.	UPDATED CABLE DIA.	12F178BG-DCA
R	03-11-13	SAT	WMA			RELEASED FOR CUSTOMER APPROVAL	12F178BG-DCA
REV	DATE	BY	CHK	APR		DESCRIPTION	ECN
DRAWN BY DATE		CHK		SCALE		THIRD ANGLE PROJECTION	
SAT 03-11-13		WMA		NONE		DRAWING NUMBER: 12F178BG-DCA	
						SHT 1 OF 1	
						SIZE D	