


QuickNet™ 8-Fiber Interconnect Cable Assemblies

technical information

8-fiber interconnect assemblies are used in high density, high speed network and storage applications. The 8-fiber MPO female connectors are compatible with QSFP fiber modules that employ parallel optics technologies such as 40GBASE-SR4 and 100GBASE-SR4. 8-fiber interconnects can connect (2) QSFP modules directly, or can be used to connect a QSFP port to an MPO-to-LC cassette.



application

8-fiber interconnects connect to QSFP modules that employ parallel optics technologies such as 40GBASE-SR4 and 100GBASE-SR4.

construction

Cable type:	3.0mm indoor
Cable jacket ratings:	Optical Fiber Nonconductive Plenum (OFNP) Low Smoke Zero Halogen (LSZH)
Fiber types:	Singlemode: OS1/OS2 9/125 μ m Multimode: OM3 50/125 μ m OM4 50/125 μ m
Connector types:	8F MPO female 8F MPO male 8F PanMPO™ Female Connector 8F PanMPO™ Male Connector
Fiber count:	8
Jacket color:	OS1/OS2: Yellow OM3: Aqua OM4: Aqua

optical properties

Maximum cable attenuation:	Singlemode: 1.0dB/km at 1310/1550nm Multimode: 3.0dB/km at 850nm 1.5dB/km at 1300nm
Maximum connector insertion loss:	Singlemode: 0.75dB Multimode: 0.35dB
Minimum connector return loss:	Singlemode: 55dB Multimode: OM3 26dB OM4 26dB

physical properties

Cable outside diameter (OD):	3.0mm
Minimum bend radius:	Under load: 20 x cable OD Static: 10 x cable OD
Cable tensile strength:	22N
Cable compressive load:	35N/cm
Cable flex:	25 cycles
Cable twist:	10 cycles
Connector durability:	500 mating cycles

environmental properties

Storage and shipping temperature:	-40°C to 70°C
Installation temperature:	0°C to 40°C
Operating temperature:	0°C to 70°C

standards

Meets or exceeds ISO/IEC 11801, TIA/EIA-568-C.3, TIA-604-5 (FOCIS-5), TIA/EIA-568-C.1
RoHS Compliant

QuickNet™ 8-Fiber Interconnect Cable Assemblies

part number

Character	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
Example	F	Z	8	R	P	J	N	J	N	X	N	F	0	0	7

1 – Fiber Product

F = Fiber

2 – Fiber Type

9 = OS1/2 9/125

X = OM3 50/125

Z = OM4 50/125

3 – Fiber Count

8 = 8-fiber

4 – Cable Type

R = 3.0mm round indoor

5 – Jacket Type

L = Low Smoke Zero Halogen (LSZH)

P = Optical Fiber Nonconductive Plenum (OFNP)

6 – Connector Type End ‘A’

G = Singlemode 8F MPO female

H = Singlemode 8F MPO male

J = Multimode 8F PanMPO™ Female Connector

K - Multimode 8F PanMPO™ Male Connector

7 – Connector Variant

N = No variant

8 – Connector Type End ‘B’

G = Singlemode 8F MPO female

H = Singlemode 8F MPO male

J = Multimode 8F PanMPO™ Female Connector

K - Multimode 8F PanMPO™ Male Connector

9 – Connector Variant

N = No variant

10 – Construction/Performance

A = Singlemode, Method A, Standard IL

X = Multimode, Method A, Optimized IL

Y = Multimode, Method B, Optimized IL

11 – Other

N = No pulling eye

12 – Unit of Length

F = Feet (Plenum)

M = Meters (LSZH)

13, 14, 15 – Length

3 - 100 Feet (Plenum)

1 - 30 Meters (LSZH)

QuickNet™ 8-Fiber Interconnect Cable Assembly Detail



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

©2017 Panduit Corp.
ALL RIGHTS RESERVED.
FBSP127--WW-ENG
1/2017