



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



- NOTES:
- SEE TABLE 1 FOR PART NUMBERS.
 - CONNECTOR MEETS THE REQUIREMENTS OF TIA-568-C.3.
 - MPO POLARITY COMPLIES WITH METHOD "A" PER TIA 568-C.0
 - A. LSZH-RATED CABLE ASSEMBLIES MEET IEC-60332, IEC-60754 AND IEC-61034 REQUIREMENTS.
B. PLENUM RATED CABLE ASSEMBLIES MEET NFPA 262.
 - CABLE MEETS THE MECHANICAL REQUIREMENTS OF ICEA-S-83-596 AND TELCORDIA GR-409-CORE.
 - ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
 - MAXIMUM STRENGTH OF THE PULLING EYE IS 20 lbs.





TABLE 1					
	PANDUIT PART NUMBER	FIBER TYPE	FIBER COUNT	JACKET TYPE	CABLE DIAMETER (mm)
MTP	FXTYL5E5EAAMLLL	50/125 OM3	12	LSZH	4.6
	FZTYL5E5EAAMLLL	50/125 OM4			
	FXUYL5E5EAAMLLL	50/125 OM3	24	LSZH	5.1
	FZUYL5E5EAAMLLL	50/125 OM4			
	FXTYP5E5EAAMLLL	50/125 OM3	12	PLENUM	4.5
	FZTYP5E5EAAMLLL	50/125 OM4			
PANMPO	FXUY5E5EAAMLLL	50/125 OM3	24	PLENUM	5.4
	FZUY5E5EAAMLLL	50/125 OM4			
	FXTYL7E7EAAMLLL	50/125 OM3	12	LSZH	4.6
	FZTYL7E7EAAMLLL	50/125 OM4			
	FXUYL7E7EAAMLLL	50/125 OM3	24	LSZH	5.1
	FZUYL7E7EAAMLLL	50/125 OM4			
PANMPO	FXTYP7E7EAAMLLL	50/125 OM3	12	PLENUM	4.5
	FZTYP7E7EAAMLLL	50/125 OM4			
	FXUY7E7EAAMLLL	50/125 OM3	24	PLENUM	5.4
	FZUY7E7EAAMLLL	50/125 OM4			

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	06-24-13	SAT	WMA/JDK		RELEASED TO PRODUCTION	12F178BG-DC

TITLE		12 & 24 FIBER MPO TO MPO SMALL DIAMETER TRUNK CABLE WITH PULLING EYE	
CUSTOMER DRAWING			
ITEM REVISION NAME		12F178BG/01	
DATASET FILE NAME		12F178BG_DC/01B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .03 [0.8] .XXX ± .010 [0.3]		PANDUIT	
ANGLES ±		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		12F178BG-DC	
DRAWN BY	DATE	CHK	SCALE
SAT	03-11-13	WMA	NONE
SHT 1 OF 1		SIZE B	