


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	WIRE/CABLE SIZE	MATERIAL	"B" +/- .050	"C" +/- .050	COLOR	MARKER S/ROLL
H100X025H1C	22-16 AWG WIRES	GMUHS31	1.00 ( 25.40 )	0.25 ( 6.35 )	WHITE	100
H100X025H2C	22-16 AWG WIRES	GMUHS31	1.00 ( 25.40 )	0.25 ( 6.35 )	YELLOW	100
H100X034H1C	18-12 AWG WIRES	GMUHS31	1.00 ( 25.40 )	0.34 ( 8.64 )	WHITE	100
H100X034H2C	18-12 AWG WIRES	GMUHS31	1.00 ( 25.40 )	0.34 ( 8.64 )	YELLOW	100
H100X044H1C	16-10 AWG WIRES	GMUHS31	1.00 ( 25.40 )	0.44 ( 11.18 )	WHITE	100
H100X044H2C	16-10 AWG WIRES	GMUHS31	1.00 ( 25.40 )	0.44 ( 11.18 )	YELLOW	100
H100X064H1C	12-6 AWG WIRES	GMUHS31	1.00 ( 25.40 )	0.64 ( 21.34 )	WHITE	75
H100X064H2C	12-6 AWG WIRES	GMUHS31	1.00 ( 25.40 )	0.64 ( 21.34 )	WHITE	75
H100X084H1C	8-1 AWG WIRES	GMUHS31	1.00 ( 25.40 )	0.84 ( 21.34 )	WHITE	75
H100X084H2C	8-1 AWG WIRES	GMUHS31	1.00 ( 25.40 )	0.84 ( 21.34 )	YELLOW	75

1  
1

NOTES:  
1. DIMENSIONS IN [ ] ARE IN MILLIMETERS.



CAD FILENAME/LAYERS  
I00619HM\_C10697\_H100\_P1\_01.prt

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING  
P1 LABEL CASSETTE  
DIE CUT HEAT SHRINK LABEL

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± .1 (XXX) ± .025  
(.XX) ± .030 ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
1	2/9/11	RVU	RVU	ADD PN: H100X064H1C AND H2C.	6300	R		
0	4/21/08	RVU		DRAWING RELEASE	5403	R		

DRAWN BY RVU	MAT'L:	SCALE NTS
DATE 4/22/08	SEE TABLE	DRAWING NO. C10697
CHK'D RVU		DWG A SIZE