



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PART NUMBER | SEE DETAIL | "A" ±.062 | MARKER ACROSS | TUBING COLOR |
|-------------|------------|----------------|---------------|--------------|
| H200X165H1T | B | 2.00 [50.80] | 1 | WHITE |
| H100X165H1T | A | 1.00 [25.40] | 2 | WHITE |
| H200X165H2T | B | 2.00 [50.80] | 1 | YELLOW |
| H100X165H2T | A | 1.00 [25.40] | 2 | YELLOW |
| H200X165H3T | B | 2.00 [50.80] | 1 | BLACK |

5



NOTES:
1. DIMENSIONS IN () ARE IN MILLIMETERS.

| | | | |
|--|---|---|---|
| CAD FILENAME/LAYERS | | 100923NL - DC - C10437/09F | |
| <h1>PANDUIT</h1> CORP. TINLEY PARK, ILLINOIS | | | |
| CUSTOMER DRAWING H***X165H** OPTIMUM COMPUTER PRINTABLE MIL. SPEC. HEAT SHRINK MARKERS | | | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: | | UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION. | |
| (.X) ± .12 (.XXX) ± .020 (.XX) ± .062 ANGLES ± | | SCALE <h2 style="text-align: center;">NTS</h2> | |
| DRAWN BY RVU DATE 8-2-06 CHK'D | MAT'L: HEATSHRINK TUBING GMUHS31, 3.5 WIDE LINER | DRAWING NO. <h1 style="text-align: center;">C10437</h1> | DWG SIZE <h1 style="text-align: center;">A</h1> |

| REV | DATE | BY | CHK | DESCRIPTION | ECN | R | CUST | SUP |
|-----|---------|-----|------------|--|------|---|------|-----|
| 5 | 4/12/12 | RVU | <i>RVU</i> | REVISED ON DETAIL A, B, DESIGN TO SHOW ALL MARKERS. | 6731 | R | | |
| 4 | 12/1/10 | RVU | | Change box design. | 6230 | R | | |
| 3 | 5/21/09 | RVU | | +/- .12, +/- .062, +/- .020 WAS +/- .03, +/- .032, +/- .010. HT: 1.65 +/- .10 WAS 1.650. MAT'L, HSK TUBING GMUHS31, 3.5 WIDE LINER WAS GMUHS. ADD "A" +/- .062. REMOVED DETAIL C. VIEW UPDATE. | 5593 | R | | |