

**® Braided Expandable Sleeving – Polyethylene Terephthalate (PET)**

- Provides continuous abrasion protection for wires, cables, hoses, and tubing
- Highly flexible open weave will not trap heat or humidity
- Allows for use with irregular shapes
- Lightweight, durable protection
- Rated for use up to 257°F (125°C)
- Compliant with U.S. and European passenger rail standards



Part Number	Color	Nominal I.D.		Nominal Diameter Range		Length per reel		Std. Pkg. Qty.	Std. Ctn. Qty.
		In.	mm	In.	mm	Ft.	m		
<b>SE12P-TR0</b>	Black	0.12	3.2	0.094 – 0.250	2.4 – 6.4	200	61.0	1	4
<b>SE25P-TR0</b>	Black	0.25	6.4	0.125 – 0.375	3.2 – 9.5	200	61.0	1	4
<b>SE38P-TR0</b>	Black	0.38	9.5	0.188 – 0.500	4.8 – 15.9	200	61.0	1	4
<b>SE50P-CR0</b>	Black	0.50	12.7	0.250 – 0.750	6.4 – 19.1	100	30.5	1	4
<b>SE75P-CR0</b>	Black	0.75	19.1	0.500 – 1.25	12.7 – 31.8	100	30.5	1	4
<b>SE125P-LR0</b>	Black	1.25	31.8	0.750 – 1.50	19.1 – 38.1	50	15.2	1	4
<b>SE150P-LR0</b>	Black	1.50	38.1	1.00 – 2.13	25.4 – 57.2	50	15.2	1	4
<b>SE175P-TR0</b>	Black	1.75	44.5	1.25 – 2.75	31.8 – 69.9	200	61.0	1	2

Reel packaging may contain splices. Contact Panduit Customer Service for further information.

**® Fray Resistant Braided Expandable Sleeving**

- Fray-resistant design resists fraying when cut with scissors
- Provides continuous abrasion protection resistance for wires, cables, and tubing
- For indoor use only
- Material: Polyethylene Terephthalate
- Rated for us up to 257°F (125°C)



Part Number	Color	Nominal I.D.		Nominal Diameter Range		Length Per Reel‡		Std. Pkg. Qty.	Std. Ctn. Qty.
		In.	mm	In.	mm	Ft.	m		
<b>SE12PSC-TR0</b>	Black	0.12	3.2	0.13 – 0.25	3.2 – 6.4	200	61.0	1	4
<b>SE25PSC-TR0</b>	Black	0.25	6.4	0.16 – 0.44	4.0 – 11.1	200	61.0	1	4
<b>SE38PSC-TR0</b>	Black	0.38	9.5	0.19 – 0.63	4.8 – 15.9	200	61.0	1	4
<b>SE50PSC-CR0</b>	Black	0.50	12.7	0.25 – 0.75	6.4 – 19.1	100	30.5	1	4
<b>SE75PSC-CR0</b>	Black	0.75	19.1	0.63 – 1.0	15.9 – 25.4	100	30.5	1	4
<b>SE125PSC-LR0</b>	Black	1.25	31.8	1.0 – 1.5	25.4 – 38.1	50	15.2	1	4
<b>SE150PSC-LR0</b>	Black	1.50	38.1	1.3 – 2.0	31.8 – 50.8	50	15.2	1	4

‡Reel packaging may contain splices. Contact Panduit Customer Service for further information.

**® Heat Shrink Flame Retardant End Caps**

- Applications include insulating and protecting wires and cables
- Adhesive lined inner wall seals and provides excellent protection against moisture
- Voltage rating of 600 V
- Shrink ratio: 3:1
- Temperature range: -67°F to 230°F (-55°C to 110°C)
- Material: Adhesive lined black flame retardant cross-linked Polyolefin



Part Number	Min. Expanded I.D.		Max. Recovered I.D.		Nominal Recovered Wall Thickness		Cap Length		Std. Pkg. Qty.	Std. Ctn. Qty.
	In.	mm	In.	mm	In.	mm	In.	mm		
<b>HSECFR0.5-XY</b>	0.51	13.0	0.16	4.1	0.09	2.3	2.5	63.5	10	100
<b>HSECFR0.8-XY</b>	0.75	19.1	0.24	6.1	0.09	2.3	2.5	63.5	10	100
<b>HSECFR1.0-XY</b>	1.10	27.9	0.35	8.9	0.12	3.0	3.0	76.2	10	100
<b>HSECFR1.5-5Y</b>	1.50	38.1	0.47	11.9	0.16	4.1	3.5	88.9	5	50
<b>HSECFR2.0-5Y</b>	2.00	50.8	0.63	16.0	0.16	4.1	3.5	88.9	5	50