

A. System Overview

HSTTV Heat Shrink on Bulk Reels

B1. Cable Ties

- Applications include insulating, protecting, and color coding wires and cables

- UL Recognized, CSA Certified

B2. Cable Accessories

- Fast shrink time

- Mil Spec: AMS-DTL-23053/5 Class 3

- Voltage: 600 V

- Temperature range: -67°F to 275°F (-55°C to 135°C)

- Shrink ratio: 2:1

- For dry locations

- Flammability: Meets UL 224 VW-1

- Material: Cross-linked Polyolefin

B3. Stainless Steel Ties



C1. Wiring Duct



C2. Surface Raceway

C3. Abrasion Protection

C4. Cable Management

D1. Terminals

D2. Power Connectors

D3. Grounding Connectors

E1. Labeling Systems

E2. Labels

E3. Pre-Printed & Write-On Markers

E4. Permanent Identification

E5. Lockout/Tagout & Safety Solutions

F. Index

| Part Number | Nominal Diameter | | Min. Expanded I.D. | | Max. Recovered I.D. | | Nominal Recovered Wall Thickness | | Length Per Reel | | Color | Std. Pkg. Qty. | Std. Ctn. Qty. |
|-------------|------------------|------|--------------------|------|---------------------|-----|----------------------------------|-----|-----------------|-------|--------|----------------|----------------|
| | In. | mm | In. | mm | In. | mm | In. | mm | Ft. | m | | | |
| HSTTV05-M | 0.046 | 1.2 | 0.046 | 1.2 | 0.023 | 0.6 | 0.016 | 0.4 | 1000 | 304.8 | Black | 1 | 2 |
| HSTTV05-M2 | 0.046 | 1.2 | 0.046 | 1.2 | 0.023 | 0.6 | 0.016 | 0.4 | 1000 | 304.8 | Red | 1 | 2 |
| HSTTV05-M4 | 0.046 | 1.2 | 0.046 | 1.2 | 0.023 | 0.6 | 0.016 | 0.4 | 1000 | 304.8 | Yellow | 1 | 2 |
| HSTTV05-M6 | 0.046 | 1.2 | 0.046 | 1.2 | 0.023 | 0.6 | 0.016 | 0.4 | 1000 | 304.8 | Blue | 1 | 2 |
| HSTTV06-M | 0.063 | 1.6 | 0.063 | 1.6 | 0.031 | 0.8 | 0.017 | 0.4 | 1000 | 304.8 | Black | 1 | 2 |
| HSTTV06-M2 | 0.063 | 1.6 | 0.063 | 1.6 | 0.031 | 0.8 | 0.017 | 0.4 | 1000 | 304.8 | Red | 1 | 2 |
| HSTTV06-M4 | 0.063 | 1.6 | 0.063 | 1.6 | 0.031 | 0.8 | 0.017 | 0.4 | 1000 | 304.8 | Yellow | 1 | 2 |
| HSTTV06-M6 | 0.063 | 1.6 | 0.063 | 1.6 | 0.031 | 0.8 | 0.017 | 0.4 | 1000 | 304.8 | Blue | 1 | 2 |
| HSTTV09-M | 0.093 | 2.4 | 0.093 | 2.4 | 0.046 | 1.2 | 0.020 | 0.5 | 1000 | 304.8 | Black | 1 | 2 |
| HSTTV09-M2 | 0.093 | 2.4 | 0.093 | 2.4 | 0.046 | 1.2 | 0.020 | 0.5 | 1000 | 304.8 | Red | 1 | 2 |
| HSTTV09-M4 | 0.093 | 2.4 | 0.093 | 2.4 | 0.046 | 1.2 | 0.020 | 0.5 | 1000 | 304.8 | Yellow | 1 | 2 |
| HSTTV09-M6 | 0.093 | 2.4 | 0.093 | 2.4 | 0.046 | 1.2 | 0.020 | 0.5 | 1000 | 304.8 | Blue | 1 | 2 |
| HSTTV12-M | 0.125 | 3.2 | 0.125 | 3.2 | 0.062 | 1.6 | 0.020 | 0.5 | 1000 | 304.8 | Black | 1 | 2 |
| HSTTV12-M2 | 0.125 | 3.2 | 0.125 | 3.2 | 0.062 | 1.6 | 0.020 | 0.5 | 1000 | 304.8 | Red | 1 | 2 |
| HSTTV12-M4 | 0.125 | 3.2 | 0.125 | 3.2 | 0.062 | 1.6 | 0.020 | 0.5 | 1000 | 304.8 | Yellow | 1 | 2 |
| HSTTV12-M6 | 0.125 | 3.2 | 0.125 | 3.2 | 0.062 | 1.6 | 0.020 | 0.5 | 1000 | 304.8 | Blue | 1 | 2 |
| HSTTV19-M | 0.187 | 4.8 | 0.187 | 4.8 | 0.093 | 2.4 | 0.020 | 0.5 | 1000 | 304.8 | Black | 1 | 2 |
| HSTTV19-M2 | 0.187 | 4.8 | 0.187 | 4.8 | 0.093 | 2.4 | 0.020 | 0.5 | 1000 | 304.8 | Red | 1 | 2 |
| HSTTV19-M4 | 0.187 | 4.8 | 0.187 | 4.8 | 0.093 | 2.4 | 0.020 | 0.5 | 1000 | 304.8 | Yellow | 1 | 2 |
| HSTTV19-M6 | 0.187 | 4.8 | 0.187 | 4.8 | 0.093 | 2.4 | 0.020 | 0.5 | 1000 | 304.8 | Blue | 1 | 2 |
| HSTTV25-D | 0.250 | 6.4 | 0.250 | 6.4 | 0.125 | 3.2 | 0.025 | 0.6 | 500 | 152.4 | Black | 1 | 2 |
| HSTTV25-D2 | 0.250 | 6.4 | 0.250 | 6.4 | 0.125 | 3.2 | 0.025 | 0.6 | 500 | 152.4 | Red | 1 | 2 |
| HSTTV25-D4 | 0.250 | 6.4 | 0.250 | 6.4 | 0.125 | 3.2 | 0.025 | 0.6 | 500 | 152.4 | Yellow | 1 | 2 |
| HSTTV25-D6 | 0.250 | 6.4 | 0.250 | 6.4 | 0.125 | 3.2 | 0.025 | 0.6 | 500 | 152.4 | Blue | 1 | 2 |
| HSTTV38-T | 0.375 | 9.5 | 0.375 | 9.5 | 0.187 | 4.8 | 0.025 | 0.6 | 200 | 61.1 | Black | 1 | 2 |
| HSTTV38-T2 | 0.375 | 9.5 | 0.375 | 9.5 | 0.187 | 4.8 | 0.025 | 0.6 | 200 | 61.1 | Red | 1 | 2 |
| HSTTV38-T4 | 0.375 | 9.5 | 0.375 | 9.5 | 0.187 | 4.8 | 0.025 | 0.6 | 200 | 61.1 | Yellow | 1 | 2 |
| HSTTV38-T6 | 0.375 | 9.5 | 0.375 | 9.5 | 0.187 | 4.8 | 0.025 | 0.6 | 200 | 61.1 | Blue | 1 | 2 |
| HSTTV50-T | 0.500 | 12.7 | 0.500 | 12.7 | 0.250 | 6.4 | 0.025 | 0.6 | 200 | 61.1 | Black | 1 | 2 |
| HSTTV50-T2 | 0.500 | 12.7 | 0.500 | 12.7 | 0.250 | 6.4 | 0.025 | 0.6 | 200 | 61.1 | Red | 1 | 2 |
| HSTTV50-T4 | 0.500 | 12.7 | 0.500 | 12.7 | 0.250 | 6.4 | 0.025 | 0.6 | 200 | 61.1 | Yellow | 1 | 2 |
| HSTTV50-T6 | 0.500 | 12.7 | 0.500 | 12.7 | 0.250 | 6.4 | 0.025 | 0.6 | 200 | 61.1 | Blue | 1 | 2 |
| HSTTV75-T | 0.750 | 19.1 | 0.750 | 19.1 | 0.375 | 9.5 | 0.030 | 0.8 | 200 | 61.1 | Black | 1 | 2 |
| HSTTV75-T2 | 0.750 | 19.1 | 0.750 | 19.1 | 0.375 | 9.5 | 0.030 | 0.8 | 200 | 61.1 | Red | 1 | 2 |
| HSTTV75-T4 | 0.750 | 19.1 | 0.750 | 19.1 | 0.375 | 9.5 | 0.030 | 0.8 | 200 | 61.1 | Yellow | 1 | 2 |
| HSTTV75-T6 | 0.750 | 19.1 | 0.750 | 19.1 | 0.375 | 9.5 | 0.030 | 0.8 | 200 | 61.1 | Blue | 1 | 2 |

Order number of pieces required, in multiples of Standard Package Quantity.