


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT INVENTORY NUMBERING SYSTEM



| PANDUIT PART NUMBER | Min. Exp. I.D In. (mm) | Max. Rec. I.D In. (mm) | NOMINAL REC WALL THICKNESS In. (mm) |
|---------------------|------------------------|------------------------|-------------------------------------|
| HSTTVA12 | .125 (3.2) | .063 (1.6) | .021±.004 (.53±.102) |
| HSTTVA19 | .187 (4.8) | .093 (2.4) | .023±.004 (.58±.102) |
| HSTTVA25 | .250 (6.4) | .125 (3.2) | .029±.005 (.74±.127) |
| HSTTVA38 | .375 (9.5) | .187 (4.8) | .029±.005 (.74±.127) |
| HSTTVA50 | .500 (12.7) | .250 (6.4) | .030±.005 (.76±.127) |
| HSTTVA75 | .750 (19.0) | .375 (9.5) | .035±.005 (.89±.127) |
| HSTTVA100 | 1.000 (25.4) | .500 (12.7) | .042±.007 (1.07±.178) |
| HSTTVA150 | 1.500 (38.1) | .750 (19.0) | .047±.008 (1.19±.203) |

NOTES:

- SHRINK RATIO: 2:1
- SHRINK RATIOS ARE APPROXIMATIONS; PLEASE REFER TO TABLE 1 FOR THE EXACT MINIMUM EXPANDED AND MAXIMUM RECOVERED I.D.'S.
- MATERIAL: CROSSLINKED POLYOLEFIN WITH ADHESIVE
- COLOR: BLACK
- "ALL WARRANTIES, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. (USER IS RESPONSIBLE TO DETERMINE SUITABILITY OF PRODUCT FOR INTENDED USE.)"

| | | |
|---|-----------|---|
| DIMENSIONS IN BRACKETS ARE METRIC [mm] | | |
| CAD FILENAME/LAYERS G00239K_PB_HSTTVA_00 | | |
| PANDUIT CORP. TINLEY PARK, ILLINOIS | | |
| FLEXIBLE ADHESIVE LINED THIN WALL HEAT SHRINK (HSTTVA) | | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 [1.3] (.XXX) ±0.010 [0.25] (.XX) ±0.02 [0.5] ANGLES ± 5° | | UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION. |
| DRAWN BY LGRAVITT | MAT'L: | SCALE NONE |
| DATE 5/14/03 | SEE NOTES | DWGING NO. G00239KN |
| CHK'D <i>[Signature]</i> | | DWG SIZE A |

| | | | | | | | | |
|-----|---------|-----|--------------------|-----------------|----------|---|--------------------|-----|
| R | 5/14/03 | LGG | <i>[Signature]</i> | INITIAL RELEASE | G00239KN | R | <i>[Signature]</i> | |
| REV | DATE | BY | CHK | DESCRIPTION | ECN | R | CUST | SUP |