



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
JOS6TP00Y JOS6TP00BL	1.75 LB/10 PCS (793.35 g/10 PCS)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- DIMENSIONS IN ( ) ARE IN METRIC.
- BREAKOUTS DESIGNED TO ACCEPT MULTI-PAIR CABLES DIRECTLY WITHOUT THE USE OF RACEWAYS.
- BOX INCLUDES:
  - 1- BOX BASE
  - 1- BOX COVER
- 2- PLT1.51-M PAN-TY
  - 1- LABEL/ LABEL COVER
  - 1- MOUNTING SCREW (USED TO SECURE COVER TO BASE)
  - 2- MAGNET (ATTACHED) (CSBM-X)
  - 6- MINI-COM TX6 PLUS JACK MODULE
6. BASE MATERIAL THICKNESS= .090 (2.29)



LABEL HOLDER/ SECURITY SCREW PLACEMENT

DRAWING FILENAME	M02479BP_DC42/00C	SIZE	A
MINI-COM 6 POSITION SHUTTERED SURFACE MOUNT BOX KIT CUSTOMER DRAWING			

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
2	3-24-09	JsP	TCK	B. ADDED JOS6TP00BL TO DRAWING.	02479-042	TCK	TCK		TCK
1	8-1-07	JsP	TCK	A. REVISED INCORRECT PAN-TY P/N.	02479-042	TCK	TCK		
R	7-29-06	MDJr	MJD	RELEASED TO PRODUCTION	02479-042				

PANDUIT <sup>TM</sup> CORP. TINLEY PARK, ILL 60477	I.I. NUMBER	N/A
	PRODUCT SPEC	N/A
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .031(.8) ANGLES ±	WORK INSTRUCTION	N/A
	SCALE	NONE
DRAWN BY: MDJr DATE: 7-29-06 CHK'D: MJD	MATERIAL:	BOX: ABS DOORS: PC
PART NO. JOS6TP00Y JOS6TP00BL		DRAWING NO. 02479-042