




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
JOSD60000Y	4.00 LB/10 PCS
JOSD60000BL	(1813.0 g/10 PCS)

- NOTES:
- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
  - SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
  - DIMENSIONS IN [ ] ARE IN METRIC.
  - BREAKOUTS DESIGNED TO ACCEPT LD3/LDP3 AND LD5/LDP5 RACEWAY.
  - BOX CONTAINS:
    - 1- BOX BASE
    - 1- BOX COVER
    - 2- PLT1.5I-M PAN-TY
    - 1- LABEL/ LABEL COVER
    - 1- MOUNTING SCREW (USED TO SECURE COVER TO BASE)
    - 2- MAGNET (ATTACHED TO BOX)
    - 2- BEND RADIUS CONTROL BRIDGE
  - BASE MATERIAL THICKNESS= .090 [ 2.29 ]



PART NUMBER		JOSD60000Y, JOSD60000BL	
TITLE		MINI-COM 6 POSITION SHUTTERED DEEP SURFACE MOUNT BOX	
		CUSTOMER DRAWING	
ITEM REVISION NAME		M02479IL/00	
DATASET FILE NAME		M02479IL_DC222/00D	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		MATERIAL:	
.x ± .xx ± .03 [ .8 ]		BOX: ABS DOORS: PC	
.xxx ± .010 [ .3 ]		DRAWING NUMBER:	
ANGLES ±		02479-222	
THIRD ANGLE PROJECTION		SHT 1 OF 1	
DRAWN BY	DATE	CHK	SCALE
JSP	4-25-07	TCK	NONE
REV	DATE	BY	CHK
2	5/29/14	JSP	REFR
		MMR	
DESCRIPTION		ECN	
REVISED AND REDRAWN, PREVIOUS REVISIONS HAVE BEEN OMITTED.		02479-222	

D10100DA/14