


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



- NOTES:
1. TERMINATED WITH (8 POSITION) UTP MODULAR PLUGS ON BOTH ENDS PER T568B.
 2. CONSTRUCTED WITH 4-PR/26AWG STRANDED F/UTP CAT6A PATCH CABLE
 3. MATERIAL:
 PLUG: POLYCARBONATE
 BOOT: THERMOPLASTIC RESIN
 4. FLAMMABILITY RATING: CM/LSZH DUAL RATED

T568B WIRING SCHEME

PLUG POSITION:	CABLE WIRE:
1	WHITE/ORANGE
2	ORANGE
3	WHITE/GREEN
4	BLUE
5	WHITE/BLUE
6	GREEN
7	WHITE/BROWN
8	BROWN

CABLE COLORS	** = COLOR
OFF WHITE	--
BLACK	BL
BLUE	BU
RED	RD
YELLOW	YL
GREEN	GR
GRAY	GY

PANDUIT PART NUMBER	MIN. CABLE LENGTH
NK6APC3**	3 FT
NK6APC5**	5 FT
NK6APC7**	7 FT
NK6APC10**	10 FT
NK6APC14**	14 FT
NK6APC20**	20 FT
NK6APC1M**	1 METER
NK6APC2M**	2 METERS
NK6APC3M**	3 METERS
NK6APC4M**	4 METERS
NK6APC5M**	5 METERS
NK6APC7M**	7 METERS
NK6APC10M**	10 METERS
NK6APC15M**	15 METERS

PART NUMBER NK6APCXX**		
TITLE NETKEY CATEGORY 6A UTP PATCH CORD		
CUSTOMER DRAWING		
ITEM REVISION NAME 14M504BB/00		PANDUIT
DATASET FILE NAME 14M504BB_DC02/00A		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL: SEE NOTE 3
.X ± .xxx ± .010 [.3] .XX ± .03 [.8] ANGLES ±		DRAWING NUMBER: 14M504BB-02
THIRD ANGLE PROJECTION		
DRAWN BY BJN	DATE 10-21-14	CHK SCAL SCALE NONE
SHT 1 OF 1		SIZE A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
R	10-21-14	BJN	SCAL	LPH	RELEASED TO PRODUCTION	14M504BB-02

D10100DA/14

2

1

2

1