






PANDUIT P/N	WEIGHT
P12B47M	4.9kg



- NOTES:
- IDENTIFICATION:
 

UNIT TYPE:	BASIC
ORIENTATION:	HORIZONTAL, 1U
OUTLET QTY&TYPE:	(12) C13
BREAKER QTY&TYPE:	(2) 20AMP, DOUBLE-POLE
INPUT VOLTAGE:	200-240VAC
INPUT CURRENT:	30A (24A DERATED)
INPUT PHASE:	SINGLE-PHASE
RATED POWER:	5.0kVA
INPUT PLUG:	NEMA L6-30P
INPUT CORD LENGTH:	3m [10']
  - ACCESSORIES:
    - POCKET GUIDE
    - QTY: (4) M6 X 12 PAN HEAD MACHINE SCREWS
    - QTY: (4) M6 CAGED NUT
  - RoHS COMPLIANT
  - VISIT PANDUIT'S ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR ADDITIONAL PRODUCT INFORMATION CONTAINED IN THE SPECIFICATION SHEET AS WELL AS A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
  - MAXIMUM ALLOWABLE INPUT POWER = 5.0 kW
  - INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01B	08/21/2017	JIANG	MIM	EDM	REVISED TOLERANCES	P12B47M
01A	06/28/2017	JIANG	MIM	EDM	INITIAL RELEASE	P12B47M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN
		DATE
		PRINT
TITLE BASIC SERIES PDU P12B47M CUSTOMER DRAWING		
ITEM REVISION NAME:		<b>PANDUIT</b>
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		DRAWING NUMBER: P12B47M_DC
DRAWN BY: JIANG	DATE: 05/24/2017	SCALE: NONE
CHK: SEAN		SHT 1 OF 1
		SCALE: B