


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	LEGENDS	"A" WIDHT +/- .062	CARDS PER LEGEND	MARKERS PER CARD	STANDARD PKG. QTY.	STANDARD CTN. QTY.	REF. CUSTOMER DRAWING
PCMCP-1-25*	1 THRU 25	.25 [6.35]	1 EACH	36	1	4	C10796
PCMCP-26-50*	26 THRU 50	.25 [6.35]	1 EACH	36	1	4	C10796
PCMCP-51-75*	51 THRU 75	.25 [6.35]	1 EACH	36	1	4	C10796
PCMCP-76-100*	76 THRU <u>99</u>	.25 [6.35]	1 EACH	36	1	4	C10796
	100	.36 [9.14]	1 EACH	25	1	4	C10796
PCMCP-101-125*	101 THRU 125	.36 [9.14]	1 EACH	25	1	4	C10796
PCMCP-126-150*	125 THRU 150	.36 [9.14]	1 EACH	25	1	4	C10796
PCMCP-A-Z**	A THRU Z	.25 [6.35]	1 EACH	36	1	4	C10796

MARKER SIZE:
 FULL SIZE MARKER - 1.50" [38.10mm]. MAX. WIRE O.D. .38 [9.50mm]
 *ONE CARD EACH NUMBER, 25 CARDS PER PACKAGE.
 **ONE CARD EACH LETTER, 26 CARDS PER PACKAGE.

CHARACTERS TO BE UNDERLINE:
99, 66, 9, 6,
86, 89, 68, 98, 16,
19, 61, 91, 60 and 90.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	MATERIAL:	DRAWING NUMBER:	SIZE	
							PCMCP-**-*** COMBINATION PACKS PCM TYPE CUSTOMER DRAWING				
							ITEM REVISION NAME 100295CA/07	PANDUIT			
							DATASET FILE NAME 100295CA_DC_C10657/07B				
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .12 [3.05] .xxx ± .025 [.635] .xx ± .062 [1.57] ANGLES ±	NONE			
1	10/11/16	RVU	SEWH	JHAC	ADD UNDER LINE TO <u>99</u> , <u>66</u> , <u>9</u> , <u>6</u> , <u>86</u> , <u>89</u> , <u>68</u> , <u>98</u> , <u>16</u> , <u>19</u> , <u>61</u> , <u>91</u> , <u>60</u> and <u>90</u> .	GAECN03662					
0	11/3/09	RVU	SEWH	MSAD	DRAWING RELEASE.	5859			C10657		
							THIRD ANGLE PROJECTION				
							DRAWN BY RVU	DATE 10/22/09	CHK JHAC	SCALE NTS	SHT 1 OF 1

D101000DA/16