


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART No.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	MATERIAL	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
PLT510	.50 (12.7)	5.0 (127.0)	0.75 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	20.1 (511)	250 (1112)	NATURAL	3.1 (1406)
PLT510B	.50 (12.7)	5.0 (127.0)	0.75 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	20.1 (511)	250 (1112)	BLACK	3.1 (1406)
PLT550	.50 (12.7)	6.0 (152.4)	0.75 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	22.2 (564)	250 (1112)	NATURAL	3.6 (1633)
PLT550B	.50 (12.7)	6.0 (152.4)	0.75 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	22.2 (564)	250 (1112)	BLACK	3.6 (1633)

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00	8/07/18	BWG	MPH	JADE	DRAWING RELEASED.	037522/00

TITLE  
**JAPANESE 100 SERIES  
PAN-TY CABLE TIE**  
CUSTOMER DRAWING

ITEM REVISION NAME  
00162NBR/00

DATASET FILE NAME  
00162NBR\_DC\_REV00

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE: IN (mm)  
.x ± .1 (2.5)      .xxx ± .010 (.25)  
.xx ± .02 (.5)      ANGLES ± ---

MATERIAL:  
**NYLON 6/6**

DRAWING NUMBER:  
00162NBR\_DC

THIRD ANGLE PROJECTION

DRAWN BY: BWG    DATE: 8/07/18    CHK: JADE    SCALE: NONE

SHT 1 OF 1    SIZE: A

D10100DA/16