


Flat Pan-Post™ Standoffs

- Standard EIA hole spacing allows product to be mounted with user supplied screws up to 1/4" (M6) diameter
- Organize cables in standard cabinets and racks
- Use where space is limited
- For indoor use only
- Material: Natural Nylon 6.6



| Part Number | Part Description | Std. Pkg. Qty. | Std. Ctn. Qty. |
|---|--|----------------|----------------|
| Flat Pan-Post™ Standoff for Nylon Cable Ties | | | |
| PPF2S-S25-V | Nylon 6.6 flat Pan-Post™ Standoff. Use with miniature, intermediate, and standard cross section cable ties. Dimensions 5.42"L x 1.50"H x .19"W (137.7mm x 38.1mm x 4.8mm). | 5 | 100 |
| PPF2S-S25-V69 | Flame retardant nylon 6.6 flat Pan-Post™ Standoff. Use with miniature, intermediate, and standard cross section cable ties. Material meets UL 94V-0 specifications. Dimensions 5.42"L x 1.50"H x .19"W (137.7mm x 38.1mm x 4.8mm). | 5 | 100 |
| Flat Pan-Post™ Standoff for Tak-Ty® Hook & Loop Cable Ties | | | |
| PPF2SV-S25-V | Nylon 6.6 flat Pan-Post™ Standoff. Use with Tak-Ty® Hook & Loop Cable Ties. Dimensions 5.60"L x 1.62"H x .19"W (142.2mm x 41.3mm x 4.8mm). | 5 | 100 |
| PPF2SV-S25-V69 | Flame retardant nylon 6.6 flat Pan-Post™ Standoff. Use with Tak-Ty® Hook & Loop Cable Ties. Material meets UL 94V-0 specifications. Dimensions 5.60"L x 1.62"H x .19"W (142.2mm x 41.3mm x 4.8mm). | 5 | 100 |

Pan-Post® Standoffs

- Support cable bundles above or away from surface
- For indoor use only
- Material: Natural Nylon 6.6



| Part Number | Part Description | Std. Pkg. Qty. | Std. Ctn. Qty. |
|-------------------|--|----------------|----------------|
| PP1S-S10-X | Pan-Post™ Standoff, mounting method #10/M5 screw, 1.06"L x .72"W x 1.97"H (26.9mm x 18.3mm x 50.0mm). Used with cable ties M,I,S. | 10 | 100 |
| PP1S-S12-X | Pan-Post™ Standoff, mounting method #12/M5.5 screw, 1.06"L x .72"W x 1.97"H (26.9mm x 18.3mm x 50.0mm). Used with cable ties M,I,S. | 10 | 100 |
| PP2S-S10-X | Pan-Post™ Standoff, mounting method #10/M5 screw, 1.06"L x .72"W x 4.60"H (26.9mm x 18.3mm x 116.9mm). Used with cable ties M,I,S. | 10 | 100 |
| PP2S-S12-X | Pan-Post™ Standoff, mounting method #12/M5.5 screw, 1.06"L x .72"W x 4.60"H (26.9mm x 18.3mm x 116.9mm). Used with cable ties M,I,S. | 10 | 100 |

Cable tie cross section sizes: M = Miniature, I = Intermediate, S = Standard.