


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NUMBER	"A" +/- .050 WIDTH in. [mm]	"B" +/- .050 HEIGHT in. [mm]
PRS0310	3.50 [88.9]	10.00 [254.0]
PRS0710	10.00 [254.0]	7.00 [177.8]
PRS0910	10.00 [254.0]	9.00 [228.6]
PRS1410	14.00 [335.6]	10.00 [254.0]
PRS1209	9.00 [228.6]	12.00 [304.8]
PRS1420	20.00 [508.0]	14.00 [335.6]

NOTES:

1. MILLIMETERS ARE IN ().
2. 1 STANDARD PKG. PER QTY.
3. VISIT www.Panduit.com TO VIEW LEGEND IMAGES.

CAD FILENAME/LAYERS 100824CB-DC-C10977/00A

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING
SAFETY RIGID POLYETHYLENE
SIGN - PRS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .075 (.XXX) ± .020
(.XX) ± .050 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
RVU

MAT'L:

SCALE
NTS

0	12/16/11	RVU		DRAWING RELEASE.	6608	R						
---	----------	-----	--	------------------	------	---	--	--	--	--	--	--

DATE
12/16/11

GMPE1
RIGID
POLYETHYLENE

DRAWING NO.
C10977

DWG
A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
-----	------	----	-----	-------------	-----	---	------	-----