

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Engineer Grade Prismatic Reflective Aluminum

Part Number	Legend	Width (Dim "A")	Height (Dim "B")	Shape	Color
PTS065	AUTHORIZED VEHICLES ONLY	12.00 [304.8]	18.00 [457.2]	RECTANGLE	Black on White
PTS066	MOTORCYCLE PARKING ONLY				
PTS067	COMPANY VEHICLES ONLY				
PTS068	DO NOT BLOCK DRIVE				
PTS069	BACK-IN PARKING ONLY				Green on White
PTS070	EMPLOYEE PARKING ONLY				
PTS071	RESERVED FOR				
PTS072	RESERVED PARKING				
PTS073	RESERVED EMPLOYEE OF THE MONTH				
PTS074	RESERVED PARKING FOR				
PTS075	STOP	18.00 [457.2]	OCTAGON	White on Red	
PTS077	WRONG WAY	24.00 [609.6]	RECTANGLE	White on Red	
PTS079	WRONG WAY	30.00 [762.0]			
PTS082	NO TRUCKS	24.00 [609.6]		RECTANGLE	Black on White
PTS087	ONE WAY DO NOT ENTER				
PTS089	NO THRU TRAFFIC				
PTS091	SPEED LIMIT 10	12.00 [304.8]			
PTS093	SPEED LIMIT 15				
PTS095	SPEED LIMIT 20				
PTS097	SPEED LIMIT 25				
PTS099	SPEED LIMIT 50				
PTS101	SPEED LIMIT 55				

- NOTES:
 1. [] INDICATE MILLIMETERS
 2. SEE WWW.PANDUIT.COM FOR MORE INFORMATION ON LEGENDS.
 3. ALL REFERENCING SHAPES AVAILABLE ON pg. 05 of 08 and 08 of 08.

02 OF 08

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
0	4/14/16	RVU	SEWH	JHAC	DRAWING RELEASE.	GAECN03455


TITLE PTS TRAFFIC SIGNS CUSTOMER DRAWING	
ITEM REVISION NAME 100999BR/00	PANDUIT
DATASET FILE NAME 100999BR_DC_C11536/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± 0.50 [12.7] .xxx ± 0.13 [3.127] .xx ± 0.25 [6.35] ANGLES ± 5 °	
MATERIAL: REFLECTIVE ALUMINUM	
DRAWING NUMBER: C11536	
DRAWN BY RVU	DATE 4/14/16
CHK JHAC	SCALE NTS
SHT 02 OF 08	
SIZE A	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Engineer Grade Prismatic Reflective Aluminum					
Part Number	Legend	Width (Dim "A")	Height (Dim "B")	Shape	Color
PTS102	SPEED LIMIT 5	12.00 [304.8]	18.00 [457.2]	RECTANGLE	Black on White
PTS103	SPEED LIMIT 5				
PTS105	SPEED LIMIT 60				
PTS107	SPEED LIMIT 65				
PTS109	SPEED LIMIT 70				
PTS111	SPEED LIMIT 10	18.00 [457.2]	24.00 [609.6]		
PTS113	SPEED LIMIT 15				
PTS115	SPEED LIMIT 20				
PTS117	SPEED LIMIT 25				
PTS119	SPEED LIMIT 50				
PTS121	SPEED LIMIT 55				
PTS123	SPEED LIMIT 5				
PTS125	SPEED LIMIT 60	24.00 [609.6]	30.00 [762.0]		
PTS127	SPEED LIMIT 65				
PTS129	SPEED LIMIT 70				
PTS131	SPEED LIMIT 50				
PTS133	SPEED LIMIT 55	24.00 [609.6]	24.00 [609.6]		
PTS135	SPEED LIMIT 60				
PTS137	SPEED LIMIT 65				
PTS139	SPEED LIMIT 70	30.00 [762.0]	30.00 [762.0]		
PTS141	YIELD				
PTS143	YIELD			TRIANGLE	Red on White

- NOTES:
 1. [] INDICATE MILLIMETERS
 2. SEE WWW.PANDUIT.COM FOR MORE INFORMATION ON LEGENDS.
 3. ALL REFERENCING SHAPES AVAILABLE ON pg. 05 of 08 and 08 of 08.

03 OF 08

						TITLE PTS TRAFFIC SIGNS CUSTOMER DRAWING						
						ITEM REVISION NAME 100999BR/00						
						DATASET FILE NAME 100999BR_DC_C11536/00A						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± 0.50 [12.7] .xxx ± 0.13 [3.127] .xx ± 0.25 [6.35] ANGLES ± 5 °						
						MATERIAL: REFLECTIVE ALUMINUM						
0 4/14/16 RVU SEWH JHAC DRAWING RELEASE.						DRAWING NUMBER: C11536						
GAECN03455						THIRD ANGLE PROJECTION 						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY RVU	DATE 4/14/16	CHK JHAC	SCALE NTS	SHT 03 OF 08	SIZE A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Engineer Grade Prismatic Reflective Aluminum					
Part Number	Legend	Width (Dim "A")	Height (Dim "B")	Shape	Color
PST145	YIELD	36.00 [914.4]	36.00 [914.4]	TRIANGLE	Red on White
PST147	NO TEXTING WHILE DRIVING	12.00 [304.8]	18.00 [457.2]	RECTANGLE	Red/Black on White
PST149	NO TEXTING WHILE DRIVING ITS THE LAW				Red/Black on White
PST151	ENTER ONLY	18.00 [457.2]	18.00 [457.2]	SQUARE	Black on White
PST153	EXIT ONLY				Black on White
PST157	CAUTION SPEED BUMP	12.00 [304.8]		RECTANGLE	Black on Yellow
PST158	SPEED BUMP AHEAD	30.00 [762.0]	30.00 [762.0]	DIAMOND	Black on Yellow
PST159	SPEED BUMP AHEAD	24.00 [609.6]	24.00 [609.6]	DIAMOND	Black on Yellow
PST161	PEDESTRAIAN CROSSING SYMBOL				Black on Yellow
PST163	SLOW				Black on Yellow
PST165	SLOW BLIND CORNER	12.00 [304.8]	18.00 [457.2]	RECTANGLE	Black on Yellow
PST167	SLOW SPEED BUMP				Black on Yellow
PST168	CAUTION SPEED BUMPS AHEAD				Black on Yellow
PST170	PEDESTRAIN CROSSING SYMBOL	30.00 [762.0]	30.00 [762.0]	DIAMOND	Black on Yellow
PST186	STOP	24.00 [609.6]	24.00 [609.6]	OCTAGON	White on Red
PST187	STOP	30.00 [762.0]	30.00 [762.0]		White on Red

NOTES:

1. [] INDICATE MILLIMETERS
2. SEE WWW.PANDUIT.COM FOR MORE INFORMATION ON LEGENDS.
3. ALL REFERENCING SHAPES AVAILABLE ON pg. 05 of 08 and 08 of 08.

04 OF 08

						TITLE PTS TRAFFIC SIGNS CUSTOMER DRAWING				
						ITEM REVISION NAME 100999BR/00				
						DATASET FILE NAME 100999BR_DC_C11536/00A				
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± 0.50 [12.7] .xxx ± 0.13 [3.127] .xx ± 0.25 [6.35] ANGLES ± 5 °				
						MATERIAL: REFLECTIVE ALUMINUM				
0 4/14/16 RVU SEWH JHAC DRAWING RELEASE.						DRAWING NUMBER: C11536				
REV DATE BY CHK APR DESCRIPTION ECN						DRAWN BY DATE CHK SCALE SIZE RVU 4/14/16 JHAC NTS SHT 04 OF 08 A				

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


Engineer Grade Prismatic Reflective Aluminum

Part Number	Legend	Width (Dim "A")	Height (Dim "B")	Shape	Color
PST188	STOP	36.00 [914.4]	36.00 [914.4]	OCTAGON	White on Red
PST190	DO NOT ENTER	24.00 [609.6]	24.00 [609.6]	SQUARE	Red/White
PST192	DO NOT ENTER	30.00 [762.0]	30.00 [762.0]		Red/White
PST194	ONE WAY (ARROW RIGHT)	18.00 [457.2]	24.00 [609.6]	RECTANGLE	Black on White
PST196	ONE WAY (ARROW LEFT)				Green/Black on White
PST198	BUCKLE UP & DRIVE CAREFULLY				
PST200	BUCKLE UP ITS THE LAW				


NOTES:

1. [] INDICATE MILLIMETERS
2. SEE WWW.PANDUIT.COM FOR MORE INFORMATION ON LEGENDS.
3. ALL REFERENCING SHAPES AVAILABLE ON pg. 05 of 08 and 08 of 08.


05 OF 08




RECTANGLE/ SQUARE



DIAMOND



OCTAGON



TRIANGLE

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
0	4/14/16	RVU	SEWH	JHAC	DRAWING RELEASE.	GAECN03455

TITLE PTS TRAFFIC SIGNS CUSTOMER DRAWING	
ITEM REVISION NAME 100999BR/00	PANDUIT
DATASET FILE NAME 100999BR_DC_C11536/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
.x ± 0.50 [12.7] .xxx ± 0.13 [3.127] .xx ± 0.25 [6.35] ANGLES ± 5 °	
DRAWING NUMBER: C11536	
DRAWN BY RVU	DATE 4/14/16
CHK JHAC	SCALE NTS
SHT 05 OF 08	
A	


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

High Intensity Prismatic Reflective Aluminum					
Part Number	Legend	Width (Dim "A")	Height (Dim "B")	Shape	Color
PTS146	NO TEXTING WHILE DRIVING	12.00 [304.8]	18.00 [457.2]	RECTANGLE	Red/Black on White
PTS160	PEDESTRIAN CROSSING SYMBOL	24.00 [609.6]	24.00 [609.6]	DIAMOND	Black on Yellow
PTS162	SLOW				
PTS169	PEDESTRIAN CROSSING SYMBOL	30.00 [762.0]	30.00 [762.0]		


NOTES:

- [] INDICATE MILLIMETERS
- SEE WWW.PANDUIT.COM FOR MORE INFORMATION ON LEGENDS.
- ALL REFERENCING SHAPES AVAILABLE ON pg. 05 of 08 and 08 of 08.


08 OF 08




RECTANGLE/ SQUARE



DIAMOND



OCTAGON



TRIANGLE

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
0	4/14/16	RVU	SEWH	JHAC	DRAWING RELEASE.	GAECN03455

TITLE PTS TRAFFIC SIGNS CUSTOMER DRAWING	
ITEM REVISION NAME 100999BR/00	PANDUIT
DATASET FILE NAME 100999BR_DC_C11536/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± 0.50 [12.7] .xxx ± 0.13 [3.127] .xx ± 0.25 [6.35] ANGLES ± 5 °	
MATERIAL: REFLECTIVE ALUMINUM	
DRAWING NUMBER: C11536	
DRAWN BY RVU	DATE 4/14/16
CHK JHAC	SCALE NTS
SHT 08 OF 08	
SIZE A	