





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
PVQ-EPC35	0.25 LB EA. 115g EA.

- NOTES:
 1. DIMENSIONS IN BRACKETS ARE IN METRIC.
 2. PART INCLUDES:
 (1) PANVIEW IQ EXPANSION PORT CABLE 35in (PVQ-EPC35)



MODEL FILENAME m02676hb_rs485_01.s1dppt		SIZE A
DRAWING FILENAME M02676HB_DC118_00A.s1ddrw		
PanView iQ Expansion Port Cable, 35in/0.89m CUSTOMER DRAWING		
 PANDUIT™ CORP. TINLEY PARK, ILL 60477	I.L. NUMBER N/A	PRODUCT SPEC/ PKG SPEC N/A
	ALL DIMENSIONS ARE GIVEN IN INCHES. UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ±1°	
 THIRD ANGLE PROJECTION	ASSEMBLY METHOD/ TEST METHOD N/A	SCALE NONE
DRAWN BY ALP	REVIEW DRAWING NUMBERS	PART NO. PVQ-EPC35
DATE 1/31/11	MAT'L: SEE NOTES ABOVE	DRAWING NO. 02676-118 Sheet 1 of 1
CHK'D MJD		

R	1/31/11	ALP	MJD	RELEASE TO PRODUCTION	02676-118	MJD	MJD			
REV.	DATE	BY	CHK D	DESCRIPTION	ECN	ECN REV	CUS T	S U P	GM BH	