


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

P*S PART NUMBER	"A" +/- .10 in. [mm]	"B" +/- .06 HEIGHT in. [mm]	"C" +/- .06 WIDTH in. [mm]
PPS0204	9.25 [234.9]	2.25 [57.2]	4.50 [114.3]
PVS0204			
PVS0305	10.00 [254.0]	3.50 [88.9]	5.00 [127.0]

NOTES:

1. MILLIMETERS ARE IN [].
2. 2 LABELS PER CARD,
5 CARDS PER PACKAGE.
3. VISIT www.Panduit.com
to view legend images.
4. REFERENCE C10949, C10951,
C10952 FOR ADDITIONAL
PPS AND PVS STYLES.



CAD FILENAME/LAYERS 100824BP-DC-C10950/00A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
0	12/5/11	RVU		DRAWING RELEASE.	6568	R		

PANDUIT CORP. TINLEY PARK, ILLINOIS
CUSTOMER DRAWING Safety Sign
PVS and PPS STYLE 3

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .025 (.XX) ± .062 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY RVU		MAT'L:	
DATE 12/5/11	SIGN TYPE		SCALE NTS
CHK'D <i>RVU</i>	PPS PVS	MATERIAL CODE PPS - POLYESTER WITH OVERLAMINATE GMV1 VINYL	DRAWING NO. C10950
			DWG A SIZE