


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PPS PART NUMBER	"A" WIDTH in. [mm]	"B" HEIGHT in. [mm]	STD. PKG. QTY.
PPS0204	4.50 [114.3]	2.25 [57.2]	5
PPS0305	5.00 [127.0]	3.50 [88.9]	
PPS0507	7.00 [177.8]	5.00 [127.0]	
PPS0514	14.00 [355.6]	5.00 [127.0]	
PPS0410	10.00 [254.0]	4.00 [101.6]	
PPS0710	7.00 [177.8]	10.00 [254.0]	1
PPS1007	10.00 [254.0]	7.00 [177.8]	
PPS1014	14.00 [335.6]	10.00 [254.0]	
PPS1209	9.00 [228.6]	12.00 [304.8]	
PPS1420	20.00 [508.0]	14.00 [335.6]	

PVS PART NUMBER	"A" WIDTH in. [mm]	"B" HEIGHT in. [mm]	STD. PKG. QTY.
PVS0109	9.00 [228.6]	1.50 [38.1]	5
PVS0305	5.00 [127.0]	3.50 [88.9]	
PVS0404	4.00 [101.6]	4.00 [101.6]	
PVS0505	5.00 [127.0]	5.00 [127.0]	
PVS0507	7.00 [177.8]	5.00 [127.0]	
PVS0509	9.00 [228.6]	5.00 [127.0]	1
PVS0705	5.00 [127.0]	7.00 [177.8]	
PVS0710	10.00 [254.0]	7.00 [177.8]	

NOTES:

1. MILLIMETERS ARE IN [].
2. VISIT www.Panduit.com to view legend images.
3. REFERENCE C10950, C10951, C10949 FOR ADDITIONAL PPS AND PVS STYLES.

							CAD FILENAME/LAYERS	
							I00824BR-DC-C10952/01B	
							PANDUIT CORP. TINLEY PARK, ILLINOIS	
							CUSTOMER DRAWING Safety Sign PVS and PPS STYLE 1	
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .06 (.XXX) ± .015 (.XX) ± .032 ANGLES ±	
							UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
2	4/7/2014	ZSG		ADD PN: PPS0410 ON TABLE	1863	R		
1	1/26/12	RVU		ADD PN: PVS0705 ON TABLE. MOVE PVS0209 TO A50284.	6655	R		
0	12/5/11	RVU		DRAWING RELEASE.	6568	R		
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
							DRAWN BY RVU	
							DATE 12/5/11	
							CHK'D	
							MAT'L:	
							SIGN TYPE	
							MATERIAL CODE	
							PPS - POLYESTER WITH OVERLAMINATE	
							PVS GMV1 VINYL	
							SCALE NTS	
							DRAWING NO.	
							C10952	
							DWG A SIZE	