



REAR VIEW




FRONT VIEW


- NOTES:
- IDENTIFICATION: VERTICAL, MIXED (18) LOCKING C13 & (6) LOCKING C19, NETWORK-ENABLED MONITORED WITH MONITORED PER OUTLET, 208V / 60A / SINGLE PHASE PDU
 - ACCESSORY COMPONENTS: (1) QUICK-START GUIDE
 - PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [INCHES]
 - INPUT POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING. DATA CAN BE ACCESSED ON UNIT DISPLAY OR REMOTELY WHEN CONNECTED VIA ETHERNET CONNECTION
 - OUTLET LEVEL POWER (AMPS, VOLTS, POWER FACTOR, FREQUENCY) MONITORING CAN BE ACCESSED REMOTELY VIA ETHERNET CONNECTION
 - RoHS COMPLIANT
 - VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
 - MAXIMUM AVAILABLE INPUT POWER = 10.0 kW
 - INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES




SIDE VIEW



PLUG
60 AMP, 250V,
2P/3W
IEC 60309, WATERTIGHT



EIGHTEEN (18)
LOCKING RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13



SIX (6)
LOCKING RECEPTACLES
20 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	2-4-15	MRWA	GLM	EDM	RELEASED TO PRODUCTION	12V091QR

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.

THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN _____
DATE _____
PRINT _____

TITLE
SMARTZONE NETWORK-ENABLED MPO SERIES RACK PDU
Q1T2B2C3N24AFA0
CUSTOMER DRAWING

ITEM REVISION NAME
12V091QR_02.PRT

DATASET FILE NAME
12V091QR_DC/02A.PRT

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:

MATERIAL/COLOR:
N/A

DRAWING NUMBER:
12V091QR_DC

THIRD ANGLE PROJECTION

DRAWN BY: MRWA DATE: 2-4-15 CHK: GLM SCALE: NONE

SHT 1 OF 1 SIZE: B