


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SEE CHART FOR PRODUCT OPTIONS.
2. PATCH CORDS ARE HELD TOGETHER USING HLS TAK-TY STRAPS AT 12" (305mm) SPACING.
3. EACH PATCH CORD IS SEQUENTIALLY NUMBERED AT BOTH ENDS WITH PORT ID LABELS.
4. PATCH CORD ID LABELS CONTAIN PATCH CORD PERFORMANCE, PART#, LENGTH(L), AND QC#.
5. ONE SET OF PLUG PACK ID LABELS AND ONE PLF1MA-C MARKER TIE ARE INCLUDED FOR CUSTOMER APPLIED SWITCH AND PORT IDENTIFICATION. FOR PRINTABLE LABEL OPTIONS, REFER TO PANDUIT C125X030FJJ, C125X030YPT AND C125X030FJC.
6. REFER TO 03073-06 FOR PLUG PACK CUSTOMER DRAWING.


QUICKNET PLUG PACK ASSEMBLY MATRIX

QPP	A	C	B	A	B	03
QUICKNET PLUG PACK	PERFORMANCE LEVEL	FLAME/SMOKE RATING (see notes below)	CABLE COLOR	PLUG PACK CONFIGURATION	PLUG PACK COLOR	PATCH CORD ASSEMBLY LENGTH
QPP	A - CAT 6A (10Gig) UTP E - CAT 6A (10Gig)/CAT 6 STP C - CAT 6 UTP	C - CM L - LOW SMOKE ZERO HALOGEN (LSZH) D - DUAL RATING (MEETS BOTH CM AND LSZH RATING)	B - BLUE W - WHITE* G - GRAY CABLE BLACK BOOT**	R - RECESSED 6 PACK	S - SILVER	03 = 3 FEET 05 = 5 FEET 07 = 7 FEET 10 = 10 FEET 14 = 14 FEET 1M = 1 METER 2M = 2 METERS 3M = 3 METERS 5M = 5 METERS

NOTES (FLAME RATING ABOVE):

- 1) ALL UTP ASSEMBLIES AVAILABLE IN CM OR LSZH ONLY (NO DUAL RATED OPTION AVAILABLE).
- 2) ALL STP ASSEMBLIES AVAILABLE ONLY AS DUAL RATED-D (MEET BOTH CM + LSZH REQUIREMENTS).

- \* NOT AVAILABLE IN CAT6A/CAT6 STP
- \*\* ONLY AVAILABLE IN CAT6A/CAT6 STP



PART NUMBER		QPP***RS**	
TITLE			
QUICKNET RECESSED 6 POSITION		PLUG PACK ASSEMBLY	
CUSTOMER DRAWING			
ITEM REVISION NAME		M03073AB/00	
DATASET FILE NAME		M03073AB_DC05/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ±	.xxx ± .010 (.3)	DRAWING NUMBER: 03073-05	
.xx ± .03 (.8)	ANGLES ±		
THIRD ANGLE PROJECTION		SCALE	
DRAWN BY	DATE	CHK	SCALE
MDJr	11-03-08	WFMI	NONE
REV	DATE	BY	CHK
DESCRIPTION		ECN	

D10100DA/14