



General Purpose Contractor Cable Ties

- -40° to 85°C Operating Temp.
- UL Listed
- Plenum Rated AH-2 for indoor use
- Black UV Weather resistant nylon material for outdoor use
- Halogen Free Polyamide 6.6

Standard Part Number		Bulk Part Number		Length (In.)	Max. Bundle Dia. (In.)	Min. Loop Tensile Strength (Lbs.)	Std. Pkg. Qty.	Bulk Pkg. Qty.
Natural Nylon 6.6 (Indoor Use)	UV Weather Resistant Nylon 6.6 (Outdoor Use)	Natural Nylon 6.6 (Indoor Use)	UV Weather Resistant Nylon 6.6 (Outdoor Use)					
S4-18-C'	S4-18-C0	S4-18-M'	S4-18-M0	3.94	0.87	18	100	1000
S5-50-C'	S5-50-C0	S5-50-M'	S5-50-M0	4.7	0.94	50	100	1000
S6-40-C'	S6-40-C0	-	-	5.51	1.3	40	100	-
S6-18-C'	S6-18-C0	S6-18-M'	S6-18-M0	6.3	1.57	18	100	1000
S6-50-C'	S6-50-C0	S6-50-M'	S6-50-M0	6.3	1.5	50	100	1000
S7-50-C'	S7-50-C0	S7-50-M'	S7-50-M0	7.4	1.81	50	100	1000
S8-18-C'	S8-18-C0	-	-	7.87	2.09	18	100	-
S8-40-C'	S8-40-C0	-	-	7.87	2.09	40	100	-
SR8-50-C'	SR8-50-C0	-	-	7.87	1.97	50	100	-
SC8-50-S10-C*°	SC8-50-S10-C0*°	-	-	7.87	1.85	50	100	-
S8-50-C'	S8-50-C0	S8-50-M'	S8-50-M0	8.46	2.09	50	100	1000
S10-50-C'	S10-50-C0	-	-	9.84	2.36	50	100	-
S12-40-C'	S12-40-C0	-	-	11.81	2.99	40	100	-
S12-50-C'	S12-50-C0	S12-50-M'	S12-50-M0	11.81	2.99	50	100	1000
S14-120-L'	S14-120-L0	S14-120-TL'	-	14.49	4.02	120	50	250
S15-40-C'	S15-40-C0	-	-	14.57	4.02	40	100	-
S15-50-C'	S15-50-C0	-	S15-50-M0	14.57	4.02	50	100	1000
SC15-120-S25-L'°°	SC15-120-S25-L0°°	-	-	14.96	3.86	120	50	-
S17-50-C'	S17-50-C0	S17-50-M'	S17-50-M0	16.93	4.33	50	100	1000
S18-175-L'	S18-175-L0	-	-	17.71	5.2	175	50	-
S18-120-L'	S18-120-L0	-	-	17.71	5.12	120	50	-
S21-175-L'	S21-175-L0	S21-175-C'	S21-175-C0	20.71	5.51	175	50	100
S21-50-C'	S21-50-C0	S21-50-M'	S21-50-M0	20.87	5.51	50	100	1000
S21-120-L'	S21-120-L0	S21-120-C'	S21-120-C0	20.98	5.51	120	50	100
S24-120-Q'	S24-120-Q0	S24-120-L'	S24-120-L0	23.62	6.89	120	25	50
S24-175-L'	S24-175-L0	-	-	24.02	7.36	175	50	-
S30-120-X'	S30-120-X0	S30-120-L'	S30-120-L0	29.53	8.58	120	10	50
S31-175-L'	S31-175-L0	-	-	30.55	8.98	175	50	-
S32-175-L***'	S32-175-L0***'	-	-	32.09	9.41	175	50	-
S36-175-L***'	S36-175-L0***'	-	-	35.91	10.35	175	50	-
S40-175-X***'	S40-175-X0***'	S40-175-L***'	S40-175-L0***'	40.16	11.61	175	10	50
S48-175-L***^'	S48-175-L0***^'	-	-	48.03	14.37	175	50	-

*UL Recognized. **UL 181. ° Mount with #10/M5 Screw. °° Mount with #12/M5 Screw. ' Plenum Rated AH-2. ^ Gray Nylon Available S-48-175-L8