


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

- ** 1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
- 2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- 3. TERMINATED WITH (8 POSITION) SHIELDED MODULAR PLUGS ON BOTH ENDS PER T568A.
- 4. CONSTRUCTED WITH 26AWG STRANDED CAT5e F/UTP LSZH/CM PATCH CABLE. CABLE COLOR: INTERNATIONAL GRAY
- 5. MATERIAL:
 - PLUG: POLYCARBONATE
 - SHIELD: COPPER ALLOY NICKEL PLATED
 - BOOT: THERMOPLASTIC RESIN
 - CABLE: DUAL-RATED CM/LSZH
- 6. NOMINAL CABLE JACKET DIAMETER IS 0.205 IN (5.21MM).



T568A WIRING SCHEME

PLUG POSITION:	CABLE WIRE:
1	WHITE/GREEN
2	GREEN
3	WHITE/ORANGE
4	BLUE
5	WHITE/BLUE
6	ORANGE
7	WHITE/BROWN
8	BROWN

SEE SHEET 2 FOR PATCH CORD LENGTHS AND PART NUMBERS

PART NUMBER		STPCHAAMB**	
TITLE			
TX5e SHIELDED PATCH CORDS (CM/LSZH)			
CUSTOMER DRAWING			
ITEM REVISION NAME		M01895CB/00	
DATASET FILE NAME		M01895CB_DC07/00G	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)			MATERIAL: SEE NOTES
.X ±	.XXX ±	ANGLES ±	
.XX ±			DRAWING NUMBER: 01895-07
DRAWN BY		DATE	SCALE
BJN		6-4-06	NONE
CHK		SCALE	SIZE
EJH		NONE	A
SHT 1 OF 1			


REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
6	4-12-16	BJN	MDJR	SASK	Q. REMOVED BROWN COLOR FROM PRODUCT OFFERING P. UPDATED TITLE BLOCK REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY	01895-07

D10100DA/14

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TX5e SHIELDED PATCH CORDS

PART NUMBER	LENGTH(MIN) ft(m)
STPCH0.5MB**	1.64ft (0.5m)
STPCH1MB**	3.28ft (1m)
STPCH1.5MB**	4.92ft (1.5m)
STPCH2MB**	6.56ft (2m)
STPCH2.5MB**	8.20ft (2.5m)
STPCH3MB**	9.84ft (3m)
STPCH4MB**	13.12ft (4m)
STPCH5MB**	16.40ft (5m)
STPCH6MB**	19.68ft (6m)
STPCH7MB**	22.97ft (7m)
STPCH8MB**	26.25ft (8m)
STPCH9MB**	29.53ft (9m)
STPCH10MB**	32.80ft (10m)
STPCH15MB**	49.21ft (15m)
STPCH20MB**	65.62ft (20m)
STPCH25MB**	82.02ft (25m)
STPCH30MB**	98.42ft (30m)
STPCH35MB**	114.83ft (35m)
STPCH40MB**	131.23ft (40m)



CROSS-SECTIONAL VIEW OF CABLE

BOOT COLORS	** = COLOR
BLACK	BL
BLUE	BU
RED	RD
YELLOW	YL
GREEN	GR

PART NUMBER		STPCHAAMB**	
TITLE			
TX5e SHIELDED PATCH CORDS (CM/LSZH)			
CUSTOMER DRAWING			
ITEM REVISION NAME		M01895CB/00	
DATASET FILE NAME		M01895CB_DC07/00G	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.X ±		.XXX ±	
.XX ±		ANGLES ±	
DRAWN BY		THIRD ANGLE PROJECTION	
BJN		EJH	
DATE		SCALE	
6-4-06		NONE	
CHK		DRAWING NUMBER:	
EJH		01895-07	
DATE		SHT 2 OF 2	
6-4-06		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
6	4-12-16	BJN	MDJR	SASK	SEE SHEET 1 FOR REVISION HISTORY	01895-07

D10100DA/14