


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	MIN. CABLE LENGTH	WEIGHT
STPKCH3**	3 FT.	.095 LB/EACH (43.1 g/EACH)
STPKCH5**	5 FT.	.150 LB/EACH (68.0 g/EACH)
STPKCH7**	7 FT.	.205 LB/EACH (93.0 g/EACH)
STPKCH10**	10 FT.	.260 LB/EACH (117.9 g/EACH)
STPKCH14**	14 FT.	.395 LB/EACH (179.2 g/EACH)
STPKCH1M**	1 METER	.103 LB/EACH (46.6 g/EACH)
STPKCH2M**	2 METERS	.193 LB/EACH (87.4 g/EACH)
STPKCH3M**	3 METERS	.283 LB/EACH (128.4 g/EACH)
STPKCH5M**	5 METERS	.460 LB/EACH (209.0 g/EACH)

\*\* P/N CODE FOR KEYED PLUG HOUSING COLOR, CABLE COLOR AND SPECIAL KEY CONFIGURATION. SEE SHEET 2 FOR DETAILS.

NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.

T568B WIRING SCHEME

PLUG POSITION:	CABLE WIRE:
1	WHITE/ORANGE
2	ORANGE
3	WHITE/GREEN
4	BLUE
5	WHITE/BLUE
6	GREEN
7	WHITE/BROWN
8	BROWN

MODEL FILENAME M03011AD/00		SIZE A
DRAWING FILENAME M03011ES_DC71/00A		
TITLE TX5e SHIELDED KEYED PATCH CORDS CUSTOMER DRAWING		
 PANDUIT <sup>R</sup> CORP. TINLEY PARK, IL 60477	I.I. NUMBER	
	PRODUCT SPEC	
 THIRD ANGLE PROJECTION	WORK INSTRUCTION	
	SCALE	NONE
DRAWN BY MDJr	REVIEW DRAWING NUMBERS	PART NO. STPKCH***
DATE 12-10-08		DRAWING NO. 03011-71 SHEET 1 OF 2
CHK'D PBD		

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	12-22-08	MDJr	PBD	RELEASED TO PRODUCTION	03011-71		VMB		

