








THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
T702TR	8.6 LB/10 PCS (3.9 kg/10 PCS)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- THIS PRODUCT IS FEATURED WITH THE TIA/EIA COMPLIANT BEND RADIUS.
- BREAKOUTS FOR LD3, LD5, LD10, T45 AND T-70 RACEWAYS.
- COVER IS EXTENDED OUT AND DOWN AROUND SIDES OF BASE WHEN ASSEMBLED.
- USE INSERT T702TRI, FOR DIVIDED TRANSITIONS.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



PART NUMBER: T702TR	PRODUCT SPECIFICATION NUMBER: N/A
FMEA/CONTROL PLAN NUMBER: N/A	PACKAGING INSTRUCTION NUMBER: N/A
INSPECTION INSTRUCTION NUMBER: N/A	WORK INSTRUCTION NUMBER: N/A

TITLE <b>TWIN-70 TRANSITION</b> CUSTOMER DRAWING	
ITEM REVISION NAME D34866EC/03	<b>PANDUIT</b>
DATASET FILE NAME D34866EC_DC_T702TR/03	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ] .x ± .1 [ .254 ]      .xxx ± .005 [ .127 ] .xx ± .01 [ .25 ]      ANGLES ± 5 °	
MATERIAL: PVC <b>A</b>	
DRAWING NUMBER: 34866-91 <b>E</b>	
DRAWN BY DW	DATE 04-07-98
CHK HIW	SCALE NONE
SHT 1 OF 1 <b>A</b>	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
3	7-12-16	BJN	WFMI	SRI	D. UPDATED METRIC WEIGHT TO 3.9 kg/10 PCS, WAS 3.8 g/10 PCS E. UPDATED TITLE BLOCK	34866-91
2	01-13-00	JHNU	BKR	HIW	C. REVISED GEOMETRY FOR T45 BREAKOUT B. ADDED T45 TO NOTE 3	34866-91
1	07-29-99	DW	HIW	HIW	A. REVISED MATERIAL AND WEIGHT	34866-91
R	04-07-98	DW	HIW	HIW	RELEASED TO PRODUCTION	34866-91

D10100DA/14