


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	LENGTH	WEIGHT
T70C**6	72.00 ±.13 (1829 ±3.0)	.9 LB/72 IN (409 G/1829 mm)
T70C**8	96.00 ±.13 (2438 ±3.0)	1.2 LB/96 IN (545 G/2438 mm)
T70C**10	120.00 ±.13 (3048 ±3.0)	1.5 LB/120 IN (682 G/3048 mm)
T70C**2 (SEE NOTE 5)	(2000 mm ±3.0)	.98 LB/78.7 IN (447 G/2000 mm)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- THE T70C IS USED WITH THE T70B, T702B, AND TG70B.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- USE TWO (2) FEET OF T70C (COVER) FOR EVERY ONE (1) FOOT OF T702B (BASE).
- ONLY AVAILABLE OUTSIDE NORTH AMERICA.



CAD FILENAME/LAYERS D35541CA_DC-T70C-03A.PRT

PANDUIT		CORP. TINLEY PARK, ILLINOIS					
T70 RACEWAY COVER		(T70C**6, T70C**8, T70C**10, T70C**2) CUSTOMER DRAWING					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.					
(.X) ± (.XX) ±.010(.3)		SCALE NONE					
(.XX) ±.03(.8) ANGLES ±		MATERIAL:					
DRAWN BY JBA		DATE 09-19-96					
CHECKED BY CEF		PVC					
DESCRIPTION		DWB					
REV DATE BY CHK		DRAWING NO. 35541-27					
DESCRIPTION		SIZE A					
4	05-18-04	JBN BKR	G. REMOVED T70C**3 PART NUMBER F. RENAMED CAD FILE	35541-27	RGRO	RGRO	
3	04-14-00	M50 CAZ	E. REVISED NOTE 2 TO INCLUDE TG70B	35541-27	HIW	HIW	
2	10-20-98	DW HIW	D. ADDED NOTE 5 C. ADDED 3M LENGTH AND WEIGHT	35541-27	HIW	HIW	
1	07-08-98	DW HIW	A. ADDED COVER SIZES.; B. ADDED NOTE 4	35541-27	HIW	HIW	
R	09-19-96	JBA CEF	RELEASED TO PRODUCTION	35541-27	CEF		
REV	DATE	BY	CHK	ECN	CHK	CUST	SUP