


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



T568B WIRING SCHEME

PLUG POSITION:	CABLE WIRE:
1	WHITE/ORANGE
2	ORANGE
3	WHITE/GREEN
4	BLUE
5	WHITE/BLUE
6	GREEN
7	WHITE/BROWN
8	BROWN

NOTES:

1. CATEGORY 6 UTP PLUG-TO-JACK ZONE CORD
2. AVAILABLE IN RISER (CMR), PLENUM (CMP) AND LOW SMOKE ZERO HALOGEN (LSZH) FLAME RATINGS
3. TERMINATED WITH TX6 PLUS UTP MODULAR PLUG ON ONE END, AND TX6 PLUS JACK MODULE ON THE OTHER.
4. CABLE JACKET COLOR IS BLUE.
5. CONSTRUCTED WITH CAT6, 24AWG, SOLID, UTP CABLE.
6. JACK COLOR IS BLACK.
7. 100% FACTORY PERFORMANCE TESTED TO CATEGORY 6 PERMANENT LINK LIMITS.


PART NUMBER		SEE CHART ON SH2	
TITLE			
CATEGORY 6 UTP PLUG-TO-JACK ZONE CORDS			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479LP/06	
DATASET FILE NAME		M02479LP_DC303/06E	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ±		.xxx ± .010 (.3)	
.xx ± .03 (.8)		ANGLES ±	
DRAWN BY		THIRD ANGLE PROJECTION	
LZ		DATE	
3-18-06		CHK	
WJC		SCALE	
NONE		DRAWING NUMBER:	
SHT 1 OF 2		02479-303	
REV		SIZE	
DATE		A	
BY			
CHK			
APR			
DESCRIPTION			
ECN			

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
4	4-14-14	BJN	JSP	EJH	REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY	02479-303

D10100DA/14

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PLENUM SERIES PART#	PANDUIT RISER SERIES PART#	PANDUIT LSZH SERIES PART#	MINIMUM CABLE LENGTH	PANDUIT PLENUM SERIES PART#	PANDUIT RISER SERIES PART#	PANDUIT LSZH SERIES PART#	MINIMUM CABLE LENGTH
UJPBU10BLY	UJRBU10BLY	N/A	10 FT. (3.0 M.)	N/A	UJRBU10MBLY	UJLBU10MBLY	10 M. (32.8 FT.)
UJPBU15BLY	UJRBU15BLY	N/A	15 FT. (4.6 M.)	N/A	UJRBU11MBLY	UJLBU11MBLY	11 M. (36.1 FT.)
UJPBU20BLY	UJRBU20BLY	N/A	20 FT. (6.1 M.)	N/A	UJRBU12MBLY	UJLBU12MBLY	12 M. (39.4 FT.)
UJPBU25BLY	N/A	N/A	25 FT. (7.6 M.)	N/A	UJRBU13MBLY	UJLBU13MBLY	13 M. (42.7 FT.)
UJPBU30BLY	UJRBU30BLY	N/A	30 FT. (9.1 M.)	N/A	UJRBU14MBLY	UJLBU14MBLY	14 M. (45.9 FT.)
UJPBU35BLY	N/A	N/A	35 FT. (10.7 M.)	N/A	UJRBU15MBLY	UJLBU15MBLY	15 M. (49.2 FT.)
UJPBU40BLY	UJRBU40BLY	N/A	40 FT. (12.2 M.)	N/A	UJRBU16MBLY	UJLBU16MBLY	16 M. (52.5 FT.)
UJPBU45BLY	N/A	N/A	45 FT. (13.7 M.)	N/A	UJRBU18MBLY	UJLBU18MBLY	18 M. (59.1 FT.)
UJPBU50BLY	UJRBU50BLY	N/A	50 FT. (15.2 M.)	N/A	UJRBU20MBLY	UJLBU20MBLY	20 M. (65.6 FT.)
UJPBU55BLY	N/A	N/A	55 FT. (16.8 M.)	N/A	UJRBU22MBLY	UJLBU22MBLY	22 M. (72.2 FT.)
UJPBU60BLY	N/A	N/A	60 FT. (18.3 M.)	N/A	UJRBU24MBLY	UJLBU24MBLY	24 M. (78.7 FT.)
UJPBU65BLY	N/A	N/A	65 FT. (19.8 M.)	N/A	UJRBU26MBLY	UJLBU26MBLY	26 M. (85.3 FT.)
UJPBU70BLY	N/A	N/A	70 FT. (21.3 M.)	N/A	UJRBU28MBLY	UJLBU28MBLY	28 M. (91.9 FT.)
UJPBU75BLY	N/A	N/A	75 FT. (22.9 M.)	N/A	UJRBU30MBLY	UJLBU30MBLY	30 M. (98.4 FT.)
UJPBU80BLY	N/A	N/A	80 FT. (24.4 M.)	N/A	UJRBU32MBLY	UJLBU32MBLY	32 M. (105.0 FT.)
UJPBU85BLY	N/A	N/A	85 FT. (25.9 M.)	N/A	UJRBU34MBLY	UJLBU34MBLY	34 M. (111.5 FT.)
UJPBU90BLY	N/A	N/A	90 FT. (27.4 M.)	N/A	UJRBU36MBLY	UJLBU36MBLY	36 M. (118.1 FT.)
UJPBU95BLY	N/A	N/A	95 FT. (29.0 M.)	N/A	UJRBU38MBLY	UJLBU38MBLY	38 M. (124.7 FT.)
UJPBU100BLY	N/A	N/A	100 FT. (30.5 M.)	N/A	UJRBU40MBLY	UJLBU40MBLY	40 M. (131.2 FT.)
UJPBU110BLY	N/A	N/A	110 FT. (33.5 M.)	N/A	UJRBU42MBLY	UJLBU42MBLY	42 M. (137.8 FT.)
UJPBU120BLY	N/A	N/A	120 FT. (36.6 M.)	N/A	UJRBU44MBLY	UJLBU44MBLY	44 M. (144.4 FT.)
UJPBU130BLY	N/A	N/A	130 FT. (39.6 M.)	N/A	UJRBU46MBLY	UJLBU46MBLY	46 M. (150.9 FT.)
UJPBU140BLY	N/A	N/A	140 FT. (42.7 M.)	N/A	UJRBU48MBLY	UJLBU48MBLY	48 M. (157.5 FT.)
UJPBU150BLY	N/A	N/A	150 FT. (45.7 M.)	N/A	UJRBU50MBLY	UJLBU50MBLY	50 M. (164.0 FT.)
N/A	UJRBU3MBLY	UJLBU3MBLY	3 M. (9.8 FT.)				
N/A	UJRBU4MBLY	UJLBU4MBLY	4 M. (13.1 FT.)				
N/A	UJRBU5MBLY	UJLBU5MBLY	5 M. (16.4 FT.)				
N/A	UJRBU6MBLY	UJLBU6MBLY	6 M. (19.7 FT.)				
N/A	UJRBU7MBLY	UJLBU7MBLY	7 M. (23.0 FT.)				
N/A	UJRBU8MBLY	UJLBU8MBLY	8 M. (26.2 FT.)				
N/A	UJRBU9MBLY	UJLBU9MBLY	9 M. (29.5 FT.)				

PART NUMBER		SEE CHART ON SHEET 2	
TITLE			
CATEGORY 6 UTP PLUG-TO-JACK ZONE CORDS			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479LP/06	
DATASET FILE NAME		M02479LP_DC303/06E	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		MATERIAL:	
.x ± .xx ± .03 [ .8 ]		.xxx ± .010 [ .3 ]	
ANGLES ±		DRAWING NUMBER:	
		02479-303	
DRAWN BY	DATE	CHK	SCALE
LZ	3-18-06	WJC	NONE
SHT 2 OF 2			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
4	4-14-14	BJN	JSP	EJH	SEE SHEET 1 FOR REVISION HISTORY	02479-303

D10100DA/14