


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PART NUMBER | LENGTH +6" (152.4)/-2" (50.8) | WEIGHT |
|--------------|----------------------------------|-------------------------------|
| UTPCH8LR25Y | 8' (2438.4) | 1.20 LB/EACH (545 G/EACH) |
| UTPCH10LR25Y | 10' (3048) | 1.44 LB/EACH (654 G/EACH) |
| UTPCH15LR25Y | 15' (4572) | 2.05 LB/EACH (932 G/EACH) |
| UTPCH20LR25Y | 20' (6096) | 2.66 LB/EACH (1209 G/EACH) |
| UTPCH6LR25Y | 6' (1829) | .96 LB/EACH (435 G/EACH) |

NOTES:

1. SEE CURRENT CATALOG TO INDICATE PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. MATES WITH FEMALE RJ21 CONNECTOR AND 10/100 BASE T PATCH PANEL.
4. CATEGORY 5 AND POWER SUM RATED.
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.

| | | | |
|--|---------|--|-------|
| PART NUMBER | | UTPCH**LR25Y | |
| TITLE | | | |
| 25 PAIR PATCH CORD ASSEMBLY ONE 110° LEFT RJ21 MALE CONNECTOR AND ONE 110° RIGHT RJ21 MALE CONNECTOR | | | |
| CUSTOMER DRAWING | | | |
| ITEM REVISION NAME | | M02479KL/00 | |
| DATASET FILE NAME | | M02479KL_DC273/00B | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] | | MATERIAL: | |
| .x ± .xxx ± .010 [.3] | | CONNECTOR HSG: UL94 V-0 THERMOPLASTIC | |
| .xx ± .03 [.8] | | CABLE JACKET: PVC | |
| ANGLES ± | | DRAWING NUMBER: | |
| | | 02479-273 | |
| DRAWN BY | DATE | CHK | SCALE |
| NER | 3-20-06 | WJC | NONE |
| SHT 1 OF 1 | | | SIZE |
| | | | A |

| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN |
|-----|--------|-----|-----|-----|--|-----------|
| 1 | 4-7-14 | BJN | JSP | EJH | REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY | 02479-273 |

D10100DA/14