


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT PART NUMBER | MIN. CABLE LENGTH | WEIGHT |
|---------------------|-------------------|--------------------------------|
| UTPKCH3** | 3 FT. | .095 LB/EACH (43.1 g/EACH) |
| UTPKCH5** | 5 FT. | .150 LB/EACH (68.0 g/EACH) |
| UTPKCH7** | 7 FT. | .205 LB/EACH (93.0 g/EACH) |
| UTPKCH10** | 10 FT. | .260 LB/EACH (117.9 g/EACH) |
| UTPKCH14** | 14 FT. | .395 LB/EACH (179.2 g/EACH) |
| UTPKCH1M** | 1 METER | .103 LB/EACH (46.6 g/EACH) |
| UTPKCH2M** | 2 METERS | .193 LB/EACH (87.4 g/EACH) |
| UTPKCH3M** | 3 METERS | .283 LB/EACH (128.4 g/EACH) |
| UTPKCH5M** | 5 METERS | .460 LB/EACH (209.0 g/EACH) |

** P/N CODE FOR KEYED PLUG HOUSING COLOR, CABLE COLOR AND SPECIAL KEY CONFIGURATION. SEE SHEET 2 FOR DETAILS.

- NOTES:
1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.

T568B WIRING SCHEME

| PLUG POSITION: | CABLE WIRE: |
|----------------|--------------|
| 1 | WHITE/ORANGE |
| 2 | ORANGE |
| 3 | WHITE/GREEN |
| 4 | BLUE |
| 5 | WHITE/BLUE |
| 6 | GREEN |
| 7 | WHITE/BROWN |
| 8 | BROWN |

| | | | |
|---|--|----------------------------|--|
| PART NUMBER | | UTPKCH**** | |
| TITLE | | | |
| | | TX5e UTP KEYED PATCH CORDS | |
| CUSTOMER DRAWING | | | |
| ITEM REVISION NAME | | M03011ER/00 | |
| DATASET FILE NAME | | M03011ER_DC70/00B | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) | | MATERIAL: | |
| .x ± | | .xxx ± .010 (.3) | |
| .xx ± .03 (.8) | | ANGLES ± | |
| DRAWING NUMBER: | | 03011-70 | |
| DRAWN BY | | MDJr | |
| DATE | | 12-10-08 | |
| CHK | | PBD | |
| SCALE | | NONE | |
| THIRD ANGLE PROJECTION | | SHT 1 OF 2 | |
| SIZE | | A | |







| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN |
|-----|--------|-----|-----|-----|---|----------|
| 1 | 4-4-14 | BJN | JSP | EJH | REVISED & REDRAWN PREVIOUS REVS REMVD FOR CLARITY | 03011-70 |

D10100DA/14

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| **PATCH CORD COLOR/KEY CODE | | | | | |
|---|---|--|---|---|---|
| A - BLACK | B - RED | C - GREEN | D - YELLOW | E - ORANGE | F - BLUE |
|  |  |  |  |  |  |
| BL | RD | GR | YL | OR | BU |

| | | | |
|--|--|----------------------------|--|
| PART NUMBER | | UTPKCH**** | |
| TITLE | | TX5e UTP KEYED PATCH CORDS | |
| | | CUSTOMER DRAWING | |
| ITEM REVISION NAME | | M03011ER/00 | |
| DATASET FILE NAME | | M03011ER_DC70/00B | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) | | PANDUIT | |
| .x ± .xxx ± .010 (.3) | | | |
| .xx ± .03 (.8) ANGLES ± | | MATERIAL: | |
| THIRD ANGLE PROJECTION | | DRAWING NUMBER: | |
| DRAWN BY | | 03011-70 | |
| DATE | | SHT 2 OF 2 | |
| CHK | | SIZE | |
| SCALE | | A | |
| NONE | | | |

| 1 | 4-4-14 | BJN | JSP | EJH | SEE SHEET 1 FOR REVISION HISTORY | 03011-70 |
|-----|--------|-----|-----|-----|----------------------------------|----------|
| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN |

D10100DA/14

2

1