

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




FIGURE 1

NOTES:

1. TX6A-SD 10GIG UTP PLUG-TO-PLUG ZONE CORD
2. 100% PERFORMANCE TESTED TO CATEGORY 6A PERMANENT LINK LIMITS.
3. TERMINATED WITH (8 POSITION) RJ45 MODULAR PLUGS AT BOTH ENDS PER T568B
4. CONSTRUCTED WITH 26AWG SOLID CATEGORY 6A UTP RISER, PLENUM, AND LOW SMOKE ZERO HALOGEN CABLE
5. MATERIALS:
 PLUG: POLYCARBONATE
 BOOT: CLEAR PVC




FIGURE 2

SEE SHEET 2 FOR ZONE CORD LENGTHS AND PART NUMBERS

T568B WIRING SCHEME

<u>PLUG POSITION:</u>	<u>CABLE WIRE:</u>
1	WHITE/ORANGE
2	ORANGE
3	WHITE/GREEN
4	BLUE
5	WHITE/BLUE
6	GREEN
7	WHITE/BROWN
8	BROWN

PART NUMBER UXP* SERIES		PRODUCT SPEC/PKG SPEC N/A	
I.I. NUMBER N/A		WORK INSTRUCTION N/A	
TITLE TX6A-SD 10GIG UTP PLUG-TO-PLUG ZONE CORD			
CUSTOMER DRAWING			
ITEM REVISION NAME 09M129BG/01		PANDUIT	
DATASET FILE NAME 09M129BG_DC02/01A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .06 [1.5] .xxx ± .010 [.3]		DRAWING NUMBER: 09M129BG-02	
.xx ± ANGLES ±			
THIRD ANGLE PROJECTION		DRAWING NUMBER: 09M129BG-02	
DRAWN BY BJN	DATE 3-22-10	CHK KSM	SCALE NONE
REV		SHT 1 OF 2	
DATE		SIZE A	
BY			
CHK			
APR			
DESCRIPTION		ECN	
09M129BG-02			

1	12-13-13	BJN	EJH	EJH	UPDATED	09M129BG-02
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

D10100DA/14


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

10GIG SD UTP PLUG-TO-PLUG ZONE CORDS	
PART NUMBERS	PART NUMBERS
UXPPBU** (PLENUM) UXPRBU** (RISER)	UXPLWH**M (LSZH)
MIN. CABLE LENGTH	MIN. CABLE LENGTH
10 FT (120")	4 METERS (158")
15 FT (180")	5 METERS (197")
20 FT (240")	6 METERS (237")
25 FT (300")	7 METERS (276")
30 FT (360")	8 METERS (315")
35 FT (420")	9 METERS (355")
40 FT (480")	10 METERS (394")
45 FT (540")	11 METERS (434")
50 FT (600")	12 METERS (473")
55 FT (660")	13 METERS (512")
60 FT (720")	14 METERS (552")
65 FT (780")	15 METERS (591")
70 FT (840")	16 METERS (630")
75 FT (900")	18 METERS (709")
80 FT (960")	20 METERS (788")
85 FT (1020")	22 METERS (867")
90 FT (1080")	24 METERS (945")
95 FT (1140")	25 METERS (985")
100 FT (1200")	26 METERS (1024")
110 FT (1320")	28 METERS (1103")
120 FT (1440")	30 METERS (1182")
130 FT (1560")	32 METERS (1260")
140 FT (1680")	34 METERS (1339")
150 FT (1800")	36 METERS (1418")
	38 METERS (1497")
	40 METERS (1575")
	42 METERS (1654")
	44 METERS (1733")
	46 METERS (1812")
	48 METERS (1890")
	50 METERS (1969")

PLENUM, AND RISER OFFERED WITH BLUE CABLE. (FEET ONLY)
LSZH OFFERED WITH WHITE CABLE. (METERS ONLY)

STRAIN RELIEF BOOTS AVAILABLE IN CLEAR ONLY.

**=LENGTH (SEE FIGURE 2, SHEET 1)

PART NUMBER UXP* SERIES		PRODUCT SPEC/PKG SPEC N/A	
I.I. NUMBER N/A		WORK INSTRUCTION N/A	
TITLE TX6 10GIG UTP -PLUG-TO-PLUG SD ZONE CORD			
CUSTOMER DRAWING			
ITEM REVISION NAME 09M129BG/01		PANDUIT	
DATASET FILE NAME 09M129BG_DC02/01A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .06 [1.5] .xxx ± .010 [.3] .xx ± ANGLES ±		MATERIAL:	
 THIRD ANGLE PROJECTION		DRAWING NUMBER: 09M129BG-02	
DRAWN BY BJN	DATE 3-22-10	CHK KSM	SCALE NONE
REV		SHT 2 OF 2	
DATE		SIZE A	

1	12-13-13	BJN	EJH	EJH	SEE SHEET 1 FOR REVISIONS	09M129BG-02
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

B

B

A

A

D10100DA/14