

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




FIGURE 1

T568B WIRING SCHEME

| PLUG POSITION: | CABLE WIRE:  |
|----------------|--------------|
| 1              | WHITE/ORANGE |
| 2              | ORANGE       |
| 3              | WHITE/GREEN  |
| 4              | BLUE         |
| 5              | WHITE/BLUE   |
| 6              | GREEN        |
| 7              | WHITE/BROWN  |
| 8              | BROWN        |

NOTES:

1. TX6A 10GIG UTP PLUG-TO-JACK ZONE CORD
2. 100% PERFORMANCE TESTED TO CATEGORY 6A PERMANENT LINK LIMITS
3. TERMINATED AT ONE END WITH (8 POSITION) RJ45 MODULAR PLUG PER T568B AND AT OTHER END WITH TX6A 10GIG JACK
4. CONSTRUCTED WITH 23AWG SOLID CATEGORY 6A RISER, PLENUM, OR LOW SMOKE ZERO HALOGEN CABLE.
5. MATERIALS:  
 PLUG: POLYCARBONATE  
 BOOT: CLEAR PVC  
 JACK HOUSING: ABS

IDENTIFICATION LABEL

TANGLE-FREE LATCH




FIGURE 2

TX6A 10GIG JACK MODULE, BLACK (CJ6X88TGBL)

SEE SHEET 2 FOR ZONE CORD LENGTHS AND PART NUMBERS

|   |                       |                                       |                      |
|---|-----------------------|---------------------------------------|----------------------|
| PART NUMBER<br><b>UZJ* SERIES</b>                               |                       | PRODUCT SPEC/PKG SPEC<br>N/A          |                      |
| I.I. NUMBER<br>N/A  |                       | WORK INSTRUCTION<br>N/A               |                      |
| TITLE<br><b>TX6A 10GIG UTP PLUG-TO-JACK ZONE CORD</b>           |                       |                                       |                      |
| CUSTOMER DRAWING  |                       |                                       |                      |
| ITEM REVISION NAME<br><b>10M185BD/00</b>                        |                       | <b>PANDUIT</b>                        |                      |
| DATASET FILE NAME<br><b>10M185BD_DC02/00B</b>                   |                       |                                       |                      |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] |                       | MATERIAL:<br><b>SEE NOTES</b>         |                      |
| .x ± .06 [ 1.5 ]      .xxx ± .010 [ .3 ]                        |                       | DRAWING NUMBER:<br><b>10M185BD-02</b> |                      |
| .xx ±      ANGLES ±   |                       |                                       |                      |
| THIRD ANGLE PROJECTION  |                       |                                       |                      |
| DRAWN BY<br><b>BJN</b>  | DATE<br><b>8-3-10</b> | CHK<br><b>MKY</b>                     | SCALE<br><b>NONE</b> |
| REV   |                       | SHT 1 OF 2                            |                      |
| DATE  |                       | SIZE<br><b>A</b>                      |                      |

| REV | DATE     | BY  | CHK | APR  | DESCRIPTION            | ECN         |
|-----|----------|-----|-----|------|------------------------|-------------|
| 1   | 12-13-13 | BJN | EJH | EJH  | UPDATED                | 10M185BD-02 |
| R   | 8-3-10   | BJN | MKY | JPMC | RELEASED TO PRODUCTION | 10M185BD-02 |

D10100DA/14

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


10GIG UTP PLUG-TO-JACK ZONE CORDS

| PART NUMBERS        |  | PART NUMBERS       |  |
|---------------------|--|--------------------|--|
| UZJPBU**BL (PLENUM) |  | UZJLWH**MBL (LSZH) |  |
| UZJRBU**BL (RISER)  |  |                    |  |
| MIN. CABLE LENGTH   |  | MIN. CABLE LENGTH  |  |
| 10 FT (120")        |  | 4 METERS (158")    |  |
| 15 FT (180")        |  | 5 METERS (197")    |  |
| 20 FT (240")        |  | 6 METERS (237")    |  |
| 25 FT (300")        |  | 7 METERS (276")    |  |
| 30 FT (360")        |  | 8 METERS (315")    |  |
| 35 FT (420")        |  | 9 METERS (355")    |  |
| 40 FT (480")        |  | 10 METERS (394")   |  |
| 45 FT (540")        |  | 11 METERS (434")   |  |
| 50 FT (600")        |  | 12 METERS (473")   |  |
| 55 FT (660")        |  | 13 METERS (512")   |  |
| 60 FT (720")        |  | 14 METERS (552")   |  |
| 65 FT (780")        |  | 15 METERS (591")   |  |
| 70 FT (840")        |  | 16 METERS (630")   |  |
| 75 FT (900")        |  | 18 METERS (709")   |  |
| 80 FT (960")        |  | 20 METERS (788")   |  |
| 85 FT (1020")       |  | 22 METERS (867")   |  |
| 90 FT (1080")       |  | 24 METERS (945")   |  |
| 95 FT (1140")       |  | 26 METERS (1024")  |  |
| 100 FT (1200")      |  | 28 METERS (1103")  |  |
| 110 FT (1320")      |  | 30 METERS (1182")  |  |
| 120 FT (1440")      |  | 32 METERS (1260")  |  |
| 130 FT (1560")      |  | 34 METERS (1339")  |  |
| 140 FT (1680")      |  | 36 METERS (1418")  |  |
| 150 FT (1800")      |  | 38 METERS (1497")  |  |
|                     |  | 40 METERS (1575")  |  |
|                     |  | 42 METERS (1654")  |  |
|                     |  | 44 METERS (1733")  |  |
|                     |  | 46 METERS (1812")  |  |
|                     |  | 48 METERS (1890")  |  |
|                     |  | 50 METERS (1969")  |  |

PLENUM, AND RISER OFFERED WITH BLUE CABLE. (FEET ONLY)  
LSZH OFFERED WITH WHITE CABLE. (METERS ONLY)

STRAIN RELIEF BOOTS AVAILABLE IN CLEAR ONLY.

\*\*=LENGTH (SEE FIGURE 2, SHEET 1)

|   |                       |                                       |                      |
|---|-----------------------|---------------------------------------|----------------------|
| PART NUMBER<br><b>UZJ* SERIES</b>   |                       | PRODUCT SPEC/PKG SPEC<br>N/A          |                      |
| I.I. NUMBER<br>N/A  |                       | WORK INSTRUCTION<br>N/A               |                      |
| TITLE<br><b>TX6A 10GIG UTP PLUG-TO-JACK ZONE CORD</b>   |                       |                                       |                      |
| CUSTOMER DRAWING  |                       |                                       |                      |
| ITEM REVISION NAME<br><b>10M185BD/00</b>  |                       | <b>PANDUIT</b>                        |                      |
| DATASET FILE NAME<br><b>10M185BD_DC02/00B</b>   |                       |                                       |                      |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN [ mm ]  |                       | MATERIAL:<br><b>SEE NOTES</b>         |                      |
| .x ± .06 [ 1.5 ]      .xxx ± .010 [ .3 ]  |                       | DRAWING NUMBER:<br><b>10M185BD-02</b> |                      |
| .xx ±      ANGLES ±   |                       |                                       |                      |
| <br>THIRD ANGLE PROJECTION |                       |                                       |                      |
| DRAWN BY<br><b>BJN</b>  | DATE<br><b>8-3-10</b> | CHK<br><b>MKY</b>                     | SCALE<br><b>NONE</b> |
| REV   |                       | SHT 2 OF 2                            |                      |
| DATE  |                       | A                                     |                      |

| REV | DATE     | BY  | CHK | APR  | DESCRIPTION                      | ECN         |
|-----|----------|-----|-----|------|----------------------------------|-------------|
| 1   | 12-13-13 | BJN | EJH | EJH  | SEE SHEET 1 FOR REVISION HISTORY | 10M185BD-02 |
| R   | 8-3-10   | BJN | MKY | JPMC | SEE SHEET 1 FOR REVISION HISTORY | 10M185BD-02 |

D10100DA/14