


## VERTICAL CABLE MANAGEMENT PANEL

Part Number(s): XGVCM\*\*\*

© Panduit Corp. 2021

#### **INSTALLATION INSTRUCTIONS**

V00029TS







M5x0.8 x 12mm

**Button Head Screw** 

Qty: 02

**VCMP** Panel Qty: 02

**Tool List** 



T25 Torx driver

For Technical Support: www.panduit.com/resources/install\_maintain.asp


# **Vertical Cable Management Panel (VCMP) Installation**


• Install VCMP on Front-to-Back Beams engaging tabs in the desired cage nut holes as shown in Figure 1


(O)

- Engage spring clip as shown below.
- Reverse Steps 1 & 2 when repositioning the VCMP at desired position.


#### Maximum Applied Load per Panel is 75 lbs









VCMP Tabs engage the cage nut holes on Front-to-Back Beam of cabinet frame






# Moving and Re-installing Vertical Cable Managers Align the (2) tabs at the *TOP* of the VCMP to the desired cage nut holes first



# Vertical Cable Management Panel KEEP-OUT Areas for Side Panel Interference


#### 1070mm Wide

Due to Side Panel interference, the VCMP cannot be installed 75mm (2 cage nuts over) left or right from center on 1070mm deep cabinets




### **1200mm Wide**

Due to Side Panel interference, the VCMP cannot be installed 50mm (1 cage nut over) left or right from center on 1200mm deep cabinets




## **Optional Accessories - not included**


Install D-Rings in orientation shown. (Reference Installation Instructions CM108B and CM615C for further Information.)





Install Flex-Clip 18 & L-Rings in orientation shown. (Reference Installation Instructions CM615C for further Information.)



## Install Tak-Tys through lashings in VCMP.







For Instructions in Local Languages and Technical Support:



E-mail: techsupport@panduit.com Phone: 866-405-6654