



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


















NOTES:

- 1. UL486A-UL486B LISTED/CSA CERTIFIED C22.2 No. 65, DUAL RATED AL9CU FOR ALUMINUM OR COPPER CONDUCTORS. MEETS OR EXCEEDS ANSI C119.4
- 2. VOLTAGE RATING: 600 V. MAX BUILDING WIRE, 1000 V. MAX. IN SIGNS & FIXTURES.
- 3. TEMPERATURE RATING: 90°C (AL9CU).
- 4. CONNECTOR BLOCK BODY MADE FROM ALUMINUM. CONDUCTOR PORTS ARE PREFILLED WITH AN OXIDE INHIBITING COMPOUND.
- 5. CONNECTOR TO INCLUDE ZINC PLATED STEEL CLAMPING SCREWS FOR EACH CONDUCTOR PORT.
- 6. INSULATION MATERIAL IS BLACK PVC.
- 7. INSULATION MATERIAL HAS A UL94V-0 FLAME RATING.
- 8. INSULATION MATERIAL HAS A UV-1 RATING.
- 9. CONNECTOR RATED FOR INDOOR USE ONLY.
- 10. CLAMPING SCREW ACCESS PORTS AND ALL WIRE ENTRY PORTS PROVIDED WITH REMOVEABLE PLASTIC CLOSURE PLUGS.
- 11. CLOSURE PLUG MATERIAL IS A BLACK LDPE.
- 12. CLOSURE PLUG MATERIAL DOES NOT HAVE A UV RATING OR FLAME RATING.
- 13. SEE PACKAGE LABEL FOR TIGHTENING TORQUE SPECIFICATIONS.
- 14. ONLY ONE CONDUCTOR PER PORT ALLOWED.
- 15. DIMENSIONS IN BRACKETS ARE MILLIMETERS.
- 16. PKG. QTY. = 12

							MULTI-TAP BLACK INSULATED CONNECTOR, SINGLE SIDI BLKPSB4-2S SERIES	ED
							CUSTOMER DRAWING	
\vdash				1	REVISED NOTE 7: UL94V-0		ITEM REVISION NAME 13J051CX/03	
03	8/16	JHNU	BKR	RGB	REVSIED NOTE 12: ADDED UV RATING ADDED UV-1 RATING NOTE	13J051CX-DC	DATASET FILE NAME 13J051CX-DC/03.SLDDRW	<u> </u>
-		ļ			ADDED INDOOR USE ONLY NOTE		UNLESS OTHERWISE SPECIFIED, MATERIAL	
02	1/16	JHNU	BKR	RGB	REVISED NOTE 5: ZINC PLATED STEEL WAS TIN PLATED ALUMINUM	13J051CX-DC	DIMENSIONAL TOLERANCES ARE: IN [mm]	
01	1/16	JHNU	BKR	RGB	ADDED PACKAGING QTY. TO PART NUMBER	13J051CX-DC	.X ± .XXX ± .XXX ± .XXX ± .XXX ± .02 [0.5] ANGLES ±	
00	12/15	JHNU	BKR	RGB	DRAWING RELEASED	13J051CX-DC	THIRD ANGLE PROJECTION DRAWING NUMBER 13J051CX-I	-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE JHNU 12/15 RGB N/A SHEET 1 OF 1	B