

HIS COPY IS PROVIDED ON	A RESTRICTED BASIS AND IS NOT TO BE U	ISED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.
Material	High Conductivity Seamless Copper Tube	
Plating	Electro-Tin	
Wire Size	2/0 AWG	.59 R REF
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric	
Wire Strip Length	1-9/16 in.	PANDUIT PANDUIT POTES8"
Stud Size	1/2 in.	PANDUII  PAN
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.50±.04 .53±.02 DIA
UL Temperature Rating	90° C	.30±.04 — .33±.02 DIA
C.S.A Certified Wire Connector	Yes	2.92±.06
Panduit Color Code on Barrel	BLACK	
Panduit Die Index No. on Barrel	P45	
Alternate Industry Die Index No. ( )	(13)	





on Barrel





								CORP. TINLEY PARK, ILLINOIS
00	6/17	JHNU	JHNU	DRAWING RELEASED	021775	RGB	RGB	LCB2/0-12W-X Copper Lug - One-Hole, Long Barrel with Window
REV	DATE	BY	СНК	DESCRIPTION	ECN	-R	SUP	SCALE N/A DRAWING NO / CAD FILE LCB2/0-12W-CUST