
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

	TAB SIZE	WIRE RANGE		DIMENSIONS in. [mm]				
PANDUIT PART #		ENGLISH	METRIC	.03 L± [0,8]	W± .01 [0,3]	D± .02 [0,5]		
DR18-250	.250 X .032 [6,3 X 0,8]	22-18	0,5-1,0	.57 [14,5]	.30 [7,6]	.54 [13,7]		
DR14-250*	.250 X .032 [6,3 X 0,8]	16-14	1,5–2,5	.57 [14,5]	.30 [7,6]	.55 [14,0]		
DR10-250	.250 X .032 [6,3 X 0,8]	12–10	4,0-6,0	.61 [15,5]	.30 [7,6]	.57 [14,5]		



## **NOTES:**

B

- 1. USED FOR:
  - A. STRANDED COPPER WIRE ONLY
  - B. 302°F [150°C] MAX. OPERATING TEMPERATURE C. 10A. MÄX. (DŘ14-250 ONLY)
- 2. MATERIAL:
  - A. STAMPING: .018 [0,46] TIN PLATED BRASS
  - B. SLEEVE: TIN PLATED BRASS
- 3. INSTALLATION TOOLS:

" UL RECOGNIZED ONLY

- A. UL LISTED AND CSA CERTIFIED: CT-100A, CT-200, CT-600-A W/CT-570CH, CT-1570, CT-1701 (DR10-250 ONLY), CT-2500 W/CT-2570CH, CT-600A
- B. PANDUIT APPROVED: CT-160, CT-260
- 4. WIRE STRIP LENGTH: 9/32 \*\*\*\* [7,1 \*\*\*]
- 5. SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- 6. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT
- 7. FIRST INSERTION FORCE: 12 Lb [53 N] MAXIMUM FIRST WITHDRAWAL FORCE: 12 Lb [53 N] MAXIMUM 6 Lb [27 N] MINIMUM



LISTED 20H3 E78522

N41331BA/12

DATASET FILE NAME



CERTIFIED LR31212



B

NON-INSULATED, SLEEVED RIGHT ANGLE FEMALE DISCONNECT (250 SERIES)

CUSTOMER DRAWING ITEM REVISION NAME

				N41331BA_DC_12A				<b>FAIDUI</b>					
	12	9/16/20 BWG HPR JADE CORRECTED SECTIONED VIEWS.		088768/00	.× ±	UNLESS OTHERWI DIMENSIONAL TOLERA .x a .1 [2.54] .xx a .01 [.25]		CIFIED, RE: IN (mm) :.005 (.127)	DRAWING NUMBER:				
i					<u> </u>					THIRD ANGLE PROJECTION		A41331	_
	REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DAW BY	DATE -	- -	N.T.S.	SHEET 1 OF 1	A
									_				

2