



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



COPPER H-TAP - HTCT250-2-1 (QTY. 1)




UNIVERSAL GROUND BAR - RGRB19U (QTY. 1) INCLUDES:
- # 12-24 HEX HEAD SCREWS (QTY. 20) PRE-ASSEMBLED



FACTORY CRIMPED #6 AWG COMMON BONDING NETWORK (CBN) JUMPER WIRE ASSEMBLY (QTY. 1) INCLUDES:
LCC6-14AW (QTY. 1)
#6 AWG WIRE - GREEN/YELLOW INSULATION 96" [2438mm] LONG

NOTES:

1. RETROFIT COMMON BONDING NETWORK (CBN) JUMPER KIT - PART NUMBER: RGRKCBNJY
2. PACKAGING: 1 KIT PER BAG; 10 KITS PER BOX
3. ALL COMPONENTS THAT MAKE UP THIS KIT ARE ROHS COMPLIANT.
4. DIMENSIONS IN BRACKETS ARE MILLIMETERS.



CLEANING PAD (QTY. 1)



5cc TUBE ANTI-OXIDANT PASTE (QTY. 1)



#12-24 M6 #10-32 & M5 SLOTTED HEX-HEAD ZINC PLATED THREAD-FORMING SCREW (QTY. 2 OF EACH)



#12 FLAT WASHER (QTY. 2)

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04	8/21	JHNU	JHNU	JADE	REMOVED 16mm FROM WIRE DESCRIPTION	N41651BB-C41651
03	3/13	JHNU	JHNU	RGB	REVISED TITLE BLOCK	N41651BB-C41651
TITLE						RETOFIT RACK GROUNDING KIT (RGRKCBNJY) CUSTOMER DRAWING
ITEM REVISION NAME						N41651BB/04
DATASET FILE NAME						C41651_04.SLDDRW
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]						MATERIAL
.X ±						
.XX ±						
ANGLES ±						
THIRD ANGLE PROJECTION						
DRAWN BY: JHNU						DATE: 2/06
SCALE: CSH						DRG: NONE
SHEET 1 OF 1						SIZE: B



SEE NOTES

DRAWING NUMBER: C41651