





CT-2600/LBT, 4 TON CRIMP TOOL

This tool meets requirements for Safety for Handheld Motor-Operated Electric Tools specification UL 60745-1 and CSA C22.2 No. 60745-1.

Tool is listed under CSA file number 80103907.

Tool meets OSHA mandated electrical and mechanical product safety requirements.














VIBR

- 1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- 2. DIMENSIONS IN [ ] ARE METRIC.
- 3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF ROHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE ROHS TECHNICAL ADAPTATION COMMITEE.

- TOOL SPECIFIC NOTES:

  1. THE CT-2600/LBT BATTERY OPERATED TOOLS ARE DESIGNED TO CRIMP WITH PANDUIT CRIMP DIES.

  2. THIS TOOL CRIMPS PANDUIT COPPER COMPRESSION
- CONNECTORS USING PANDUIT CRIMPING DIES. GO TO www.panduit.com FOR MORE INFORMATION.
- THIS TOOL CAN OPERATE WITH BLUE TOOTH TECHNOLOGY TO CONNECT TO THE I-PRESS PHONE APP TO MONITOR CRIMP PERFORMANCE.


## THE CT-2600/L TOOL KIT INCLUDES:

- OTY. DESCRIPTION/ITEM
- BATTERY OPERATED 4 TON HYDRAULIC TOOL RECHARGEABLE BATTERIES (MAKITA LI-ION 18VDC, 4Ah)
- MAKITA BATTERY CHARGER 120VAC (WITH US PLUG CONFIGURATION)
- TOOL CASE

## TECHNICAL INFORMATION:

- 1. TOOL WEIGHT (INCLUDING BATTERY) 5.3 LBS. [2.4 kg] 2. DIMENSIONS (INCLUDING BATTERY) 14.2" L x 4.9" H
- × 3" W  $[360 L \times 125 H \times 75 W] mm$
- 3. CRIMPING FORCE 4 TONS [35 kN]
- 4. A COPY OF OPERATION MANUAL AND ACCESSORY INFORMATION CAN BE FOUND AT: www.panduit.com.

DIMENSIONS IN [BRACKETS] ARE IN MILLIMETERS. ALL DIMENSIONS ARE FOR REFERENCE ONLY.



A

 $\mathsf{B}$