

## THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube		
Plating	Electro-Tin		
Wire Size	500 STR/FLEX		
Wire Type	Stranded Copper: Class G, H, I, K, M, Locomotive		
Wire Strip Length	1-9/16 in.		
Stud Size	3/8 in.		
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.		
UL Temperature Rating	90°C		
C.S.A Certified Wire Connector	Yes		
Panduit Color Code on Barrel	PINK		
Panduit Die Index No. on Barrel	P99		
Alternate Industry Die Index No. ( ) on Barrel	(L99)		









						PAROUIT CORP. TINLEY PARK, ILLINOIS
04	1/11	JHNU	JHNU	REVISED OVERALL LENGTH: WAS 4.32 REVISED TONGUE THICKNESS: WAS .28		LCDXN500-38D-6 Copper Lug - Narrow Tongue, Two-Hole, Standard Flex Barrel
REV	DATE	BY	СНК	DESCRIPTION	ECN	PRAWING NO / CAD FILE LCDXN500-38D-CUST