PANDUIT®

Safety Padlocks and Kits

Safety is an essential element of risk mitigation throughout the physical infrastructure. Panduit long body non-conductive padlocks are designed specifically for lockout/tagout applications to help reduce the risk of electrical hazards while providing high security. All Panduit lockout kits, lockout stations, and the group lockout box are designed for use with non-conductive padlocks, contributing to the protection of employees from unexpected hazards while meeting safety and regulatory requirements. In addition, Panduit offers high security and custom keyed padlocks for application flexibility. These are part of a comprehensive line of safety and facility identification products to optimize workplace safety and aid in compliance.



Key Features	Benefits	
Multiple padlock styles available	Comprehensive line of padlocks provides application flexibility for enhanced workplace safety	
	Compact aluminum padlocks can be used for lockout operations in tight areas	
Customized options	Provides customized style, keying, color, and identification options to create the right padlock solution for any application	
Lockout kits	Designed specifically for lockout/tagout applications; each kit provides a selection of devices commonly used by electricians, electrical contractors, and MRO personnel to provide a full lockout solution for the application	

DISCLAIMER: The information contained herein is intended as a guide for use by persons having technical skill at their own discretion and risk. Before using, Buyer shall determine the suitability of the Panduit product for his intended use and Buyer assumes all risk and liability whatsoever in connection therewith.



Padlocks



Safety Padlocks

Padlock offering includes many customizable options. Select the style, keying, color, and identification options to create the right padlock solution for your application.

Padlock Styles



Licita Br With Eller With Eller CERRADO SUBJORT

Non-Conductive Safety Padlock

Non-Conductive Long Body Safety Padlock



Padlock



Aluminum Long Shackle Padlock



Keyed Alike and Master Keyed

Purple



Keyed Differently

Red

Color Options

Keying Options

Keyed Alike



Keyed Differently and Master Keyed







Brown

Non-Conductive Safety Padlocks

FEATU FEATU BEST SELLE FEATU Blue

Yellow



Aluminum body and shackle with non-conductive vinyl cover delivers protection against electrical hazards for maximum safety, specifically in lockout/tagout applications. Padlock is available with the standard 1.77 inches body design that allows safety message to be displayed on the padlocks in two languages.

	Body Height 1.77" (45.2mm)	Std. Pkg.
Color	Part Number	Qty.
Black	PSL-8BL	
Blue	PSL-8BU	
Brown	PSL-8BR	
Green	PSL-8GR	
Orange	PSL-80R	1
Purple	PSL-8PU	
Red	PSL-8*	
	PSL-8YL	

* PSL-8 is available in long body, part number is PSL-8-LB.

Aluminum Padlocks



PSL-7 and PSL-7-LS



PSL-12

Solid aluminum body with anodized aluminum finish design can withstand extreme environmental conditions for improved durability and enhanced corrosion resistance. These padlocks are available with standard 1.50 x 1.62 inches body or ultra-compact 1.25 x 1.37 inches body for lockout operations in tight spaces.

	Body Height 1.62" (41.1mm) Shackle Height 1.00" (25.4mm)	Body Height 1.62" (41.1mm) Shackle Height 3.00" (76.2mm)	Body Height 1.25" (31.7 mm) Shackle Height 1.00" (25.4mm)	Std. Pkg.
Color		Part Number		Qty.
Black	PSL-7BL	PSL-7BL-LS	—	
Blue	PSL-7BU	PSL-7BU-LS	—	
Green	PSL-7GR	PSL-7GR-LS	—	4
Orange	PSL-70R	PSL-70R-LS	_	
Red	PSL-7	PSL-7-LS	PSL-12	
Yellow	—	PSL-7YL-LS	—	

Specialty Padlocks



PSL-9 and PSL-9-LS

Harsh environment padlocks are created with a solid brass body with a chrome finish and stainless steel shackle for use in severe weather and environmental conditions.

Part Number	Color	Part Number	Std. Pkg. Qty.
PSL-9	Silver	Harsh environment padlock; shackle height 1.00" (25.4mm)	4
PSL-9-LS	Silver	Harsh environment padlock; shackle height 3.00" (76.2mm)	I

Electrician Lockout Kit



Part Number	Part Description	Std. Pkg. Qty.
PSL-PK-EAP	Kit includes: (1) screwdriver, (1) PSL-PK pouch, (1) PSL-8 padlock, (1) PSL-MLD multiple lockout, (1) PSL-WS wall switch lockout, (1) PSL-PCBNT PowerLOK [™] No Tool Circuit Breaker Lockout, (1) PSL-P plug lockout, (5) PVT-30 blocking tags.	
PSL-PK-EA	Kit includes: (1) screwdriver, (1) PSL-PK pouch, (1) PSL-8 padlock, (1) PSL-MLD multiple lockout, (1) PSL-WS wall switch lockout, (1) PSL-CBNT No Tool circuit breaker lockout, (1) PSL-P plug lockout, (5) PVT-30 blocking tags.	1
PSL-PK-EA-S	Kit includes: (1) screwdriver, (1) PSL-PK pouch, (1) PSL-8 padlock, (1) PSL-MLD multiple lockout, (1) PSL-WS wall switch lockout, (1) PSL-CBNT No Tool circuit breaker lockout, (1) PSL-P plug lockout, (5) PVT-30 blocking tags, English/Spanish.	

Safety Padlocks

Contractor Lockout Kit

P

Saladian	Part Number	Part Description	Std. Pkg. Qty.	
	PSL-KT-CONAP	Kit includes: (1) screwdriver, (1) PSL-KT case, (6) PSL-8 padlocks, (1) PSL-1A hasp, (1) PSL-MLD lockout, (3) PSL-WS wall switch lockout, (3) PSL-PCBNT PowerLOK [™] No Tool Circuit Breaker Lockout, (3) PSL-P plug lockouts, (15) PVT-98 tags.		
	PSL-KT-CONA	Kit includes: (1) screwdriver, (1) PSL-KT case, (6) PSL-8 padlocks, (1) PSL-1A hasp, (1) PSL-MLD lockout, (3) PSL-WS wall switch lockout, (3) PSL-CBNT No Tool circuit Breaker Lockout, (3) PSL-P plug lockouts, (15) PVT-98 tags.	1	
PSL-KT-CONAP	PSL-KT-CONA-S	Kit includes: (1) screwdriver, (1) PSL-KT case, (6) PSL-8 padlocks, (1) PSL-1A hasp, (1) PSL-MLD lockout, (3) PSL-WS wall switch lockout, (3) PSL-CBNT No Tool circuit Breaker Lockout, (3) PSL-P plug lockouts, (15) PVT-98 tags, English/Spanish.		

Maintenance Lockout Kit



PSL-KT-MROAP

Part Number	Part Description	Std. Pkg. Qty.
PSL-KT-MROAP	Kit includes: (1) screwdriver, (1) PSL-BX case, (3) PSL-8 padlocks, (1) PSL-MLD, (2) PSL-WS, (2) PSL-PCBNT PowerLOK [™] No Tool Circuit Breaker Lockout, (2) PSL-P, (1) PSL-V6A, (1) PSL-V2A, (1) PSL-BV2, (1) PSL-CL110, (10) PVT-44 maintenance tags.	
PSL-KT-MROA	Kit includes: (1) screwdriver, (1) PSL-BX case, (3) PSL-8 padlocks, (1) PSL-MLD, (2) PSL-WS, (2) PSL-CBNT No Tool "Circuit Breaker Lockout, (2) PSL-P, (1) PSL-V6A, (1) PSL-V2A, (1) PSL-BV2, (1) PSL-CL110, (10) PVT-44 maintenance tags.	1
PSL-KT-MROA-S	Kit includes: (1) screwdriver, (1) PSL-BX case, (3) PSL-8 padlocks, (1) PSL-MLD, (2) PSL-WS, (2) PSL-CBNT No Tool Circuit Breaker Lockout, (2) PSL-P, (1) PSL-V6A, (1) PSL-V2A, (1) PSLBV2, (1) "PSL-CL110, (10) PVT-44 maintenance tags, English/Spanish.	

Power and Panel Distribution Lockout Kit

	Part Number	Dout Description	Std. Pkg.
LOCKOUT	Part Number	Part Description	Qty.
TAGOUT STATION	PSL-KT-PWRP	Kit includes: (1) screwdriver, (1) PSL-STATION, (2) PSL-8 padlocks, (1) PSL-MLD, (2) PSL-PCBNT PowerLOK [™] No Tool Circuit Breaker Lockout, (2) PSL-CBILNT, (2) PSL-CBL, (1) PSL-P, (25) PVT-23-Q tags.	
6 6 N	PSL-KT-PWR	Kit includes: (1) screwdriver, (1) PSL-STATION, (2) PSL-8 padlocks, "(1) PSL-MLD, (2) PSL-CBNT No Tool Circuit Breaker Lockout, (2) PSL-CBILNT, (2) PSL-CBL, (1) PSL-P, (25) PVT-23-Q tags.	1
PSL-KT-PWRP	PSL-KT-PWR-S	Kit includes: (1) screwdriver, (1) PSL-STATION, (2) PSL-8 padlocks, (1) PSL-MLD, (2) PSL-CBNT No Tool Circuit Breaker Lockout, (2) PSL-CBILNT, (2) PSL-CBL, (1) PSL-P, (25) PVT-23-Q tags, English/Spanish	

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA	
Markham, Ontario	
cs-cdn@panduit.com	
Phone: 800.777.3300	

> PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA PAN Guadalajara, Mexico Vict cs-la@panduit.com cs-a Phone: 52.33.3777.6000 Pho

PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

PANDUIT

Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300 ©2022 Panduit Corp. ALL RIGHTS RESERVED. Printed in the U.S.A. Product Bulletin Number SFCB25-WW-ENG Replaces SFCB05--SA-ENG 02/2022