

THIS COPY IS PROVIDED ON	A RESTRICTED BASIS AND IS NOT TO BE U	ISED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.			
Material	High Conductivity Seamless Copper Tube				
Plating	Electro-Tin				
Wire Size	250 kcmil				
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric				
Wire Strip Length	1-11/16 in.	1.17±.04			
Stud Size	1/2 in.	1.17±.04 Q			
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.63±.04 1.75±.02 .5			
UL Temperature Rating	90° C	5.03±.06			
C.S.A Certified Wire Connector	Yes				
Panduit Color Code on Barrel	YELLOW				
Panduit Die Index No. on Barrel	P62	<u> </u>			
Alternate Industry Die Index No. () on Barrel	(16)	Wire inspection window			









								CORP. TINLEY PARK, ILLINOIS
								LAGODO COM . HINLET PARK, ILLINOIS
								LCC250-12W-X
01	8/12	JHNU	JHNU	REMOVED NAVY NUMBER	N10883VH-LCC250-12W-CUST	RGB	RGB	Copper Lug - Two-Hole, Long Barrel with Window
REV	DATE	BY	СНК	DESCRIPTION	ECN	-R	SUP	DRAWING NO / CAD FILE LCC250-12W-CUST