



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.*	DESCRIPTION	WEIGHT
DP24584TV25Y	25 PAIR RJ21 CONNECTOR 24 PORT 10/100BASE-T WIRED (WITH TAK-TYS)	0.90 LB (408g)

\* NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM AS WELL AS OPTIONAL SNAP-IN LABEL HOLDERS.
2. 24 PORT PATCH PANEL 2 PAIR WIRED (1,2,3,6). 8 POSITION MODULE JACK 4 POSITION WIRED.
3. THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
4. FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS AND (4) M6x1x15MM METRIC SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
5. DIMENSIONS IN [ ] ARE IN METRIC.

PART NUMBER		DP24584TV25Y	
TITLE			
24 PORT DATA-PATCH CATEGORY 5E 10/100BASE-T PATCH PANEL			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479JX/01	
DATASET FILE NAME		M02479JX_DC259/01C	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		MATERIAL:	
.X ± .XXX ± .010 [ .3 ]		PANEL: C.R.S. RJ45 HOUSING: V-0 ABS	
.XX ± .03 [ .8 ]		DRAWING NUMBER:	
ANGLES ±		02479-259	
		THIRD ANGLE PROJECTION	
DRAWN BY	DATE	CHK	SCALE
NER	3-20-06	WJC	NONE
SHT 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
3	6/11/14	JSP	REFR	MMR	REVISED AND REDRAWN, PREVIOUS REVISIONS HAVE BEEN OMITTED.	02479-259