




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
UICMPPA24BLY	.57 LB/EACH PC (257.0 g/EACH PC)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
  - 1- METAL STAMPING
  - 6- 4 POSITION FACEPLATE WITH 1 LABEL POCKET (ASSEMBLED TO METAL STAMPING)
  - 6- CLEAR LABEL COVER
  - 1- SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
5. LABELS SOLD SEPARATELY.



PART NUMBER		UICMPPA24BLY	
TITLE			
MINI-COM ULTIMATE ID ANGLED 24 PORT MODULAR PATCH PANEL WITH 1 LABEL POCKET PER FACEPLATE			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479AR/05	
DATASET FILE NAME		M02479AR_DC18/05A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		MATERIAL:	
.x ± .xx ± .03 (.8)		PANEL: C.R.S. FACEPLATE: ABS	
.xxx ± .010 (.3)		DRAWING NUMBER:	
ANGLES ±		02479-018	
THIRD ANGLE PROJECTION		SHT 1 OF 1	
DRAWN BY	DATE	CHK	SCALE
JSP	4-19-06	MJD	NONE
REV			SIZE
A			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
05A	3-8-22	BJN	MDJR	MMR	B. UPDATED CAD MODEL TO REV 05	M09000PQ
2	11-12-18	BAME	KRKE	MMR	A. REMOVED METRIC SCREWS	02479-018
1	5-8-14	BJN	JSP	MMR	REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY	02479-018

D10100DA/14

2

1

2

1