

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORPORATION.

	LICED WITH CARLE		DIMEN	SIONS	WELCHT	
PANDUIT PART NUMBER	USED WITH CABLE TIES	'A' (REF)	'B' (REF)	° C °	'D' (REF)	WEIGHT grams/100pcs
PUM-925	M, I, S, LH, H	19.6	6.6	26.7	19.1	116.4





- 1. SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, MATERIAL AND COLOR.
- 2. (*) DIMENSIONAL VARIANCE IS POSSIBLE DUE TO MOLDING PROCESS RELATED SINK MARKS.
- 3. APPLICATION SPECIFICATION:
 HOLE DIAMETER: 8.8 9.3 mm
 PANEL THICKNESS: 1.0 16.0 mm



SCALE 1.5:1

'B' (REF)

CAD FILENAME/LAYERS 10B015CY/00 DC_GB0239MQ_10

L'ANDUIT CORP

TINLEY PARK, ILLINOIS

PUM-925 PUSH UMBRELLA MOUNT 925

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE METRIC TOLERANCE: ±0.5MM

									TOLERANCE: ±0.5MM	
									DRAWN BY TMSA	MAT'L:
10	3/11/11	BWG	JADE	CHANGED MATERIAL NOTE. REMOVED MATERIAL BOX FROM CHART.	GB0239M0	10	PBC		12-29-06	NYLON 6/6
REV	DATE	ВҮ	СНК	DESCRIPTION	ECN -	R	CUST	SUP	CHK'D	

1.5:1 UNLESS NOTED

Α

:B0239M(

DRAWING NO.

GB0239MQ