# MP200 PXE SERIES Mobile Printer









## **PXE SERIES Mobile Printers**

Do your job smarter, faster and easier with PXE Series Mobile Printers. This full line of advanced identification printers combine Panduit's industry-leading performance and field-tested durability with Epson's world-class printing technology.



## **MP200 Mobile Label Printer**

Better features and performance including PC connectivity for printing from a preferred software.

#### **FEATURES:**

- Shared MP Cassette Platform
- 180 dpi print resolution
- Automatic cutter with full or half cut
- Fast 1.2 in/sec print speed
- Up to 1.0 in wide label media
- Prints continuous labels only
- USB connectivity
- Prints from Easy-Mark Plus™ Software
- Magnetic attachment accessory\*
- Rechargeable battery pack\*
- Application specific label modes



## Easy-Mark Plus™ Software\*

- Common templates to easily create and print all electrical and network applications
- 11 languages included
- Available for USB flash drive, CD, web download or network server-based version
- Works with Panduit portable and desktop thermal transfer printers, Panduit embossing systems and other laser jet and ink jet printers
- A free 90 day trial version is available from www.panduit.com

\*These features come with the MP200-KIT.





#### PORTABLE LABEL PRINTER PARTNER

## **Epson™ Print Technology**

Epson is a global technology leader dedicated to connecting people, things and information with efficient, compact and precision technologies.

## Panduit™ Labeling and Software Expertise

Panduit creates leading-edge labeling solutions for electrical and network environments, from the data center to the telecom room, the jobsite to the plant floor.





## Highlights



**Continuous Self-Laminating Labels** 



Flag Labels



Continuous Tapes



Patch Panel / Face Plate Labels



**Mixed Length Labels** 


High printing speed / Half cut function





Front loading cassette / Less margin waste





Label retention after cutting



Printer attaches to metal surfaces with included magnet

# **Ordering Information**

#### **Printers and Accessories**





Part Number	Description
MP200	The MP200 printer is a rugged, high performance, economical industrial printer. It features fast print speeds up to 1.2"/ sec, a powered cutter allowing both full and half cuts, a large LCD backlit screen, custom label modes, barcodes and symbols. The MP200 prints continuous tapes up to 1.0" wide for network, electrical, and other industrial applications. It comes with the printer, continuous label cassette, and quick reference card. For use globally.
MP200 KIT	The MP200-KIT printer is a rugged, high performance, economical industrial printer. It features fast print speeds up to 1.2"/sec, a powered cutter, a large LCD backlit screen, custom label modes, barcodes and symbols. The MP200 prints continuous tapes up to 1.0" wide for network, electrical, and other industrial applications. It comes with the printer, a continuous label cassette, hard carrying case, rechargeable battery pack, magnetic feet, USB cable, and power adapter. For use in North America.
MP-ACS-1	The MP-ACS-1 12-240 VAC Universal Power Adapter is designed for use with the MP100 and MP200 mobile printers. The universal power adapter is RoHA Compliant. The adapter is black and comes 1 per package. For use in North America.
MP-BATT	The MP-BATT Li-Lon Rechargeable Replacement Battery Pack is designed for use with the MP200 and MP300 mobile printers. The battery pack is RoHA Compliant. The battery is gray and comes 1 per package. For use in North America.
MP-CASE	The MP-CASE is a Replacement Hard Carrying Case designed for the MP200 and MP300 mobile printers. The case is RoHA Compliant. The case is 15.57 inches L x 11.74 inches W (395.4 mm x 298.4 mm). It is black and comes 1 per package.

DAY PARAGORA DAY PARAGORA EMPLUS

Part Number	Description
EMPLUS-CD	Easy-Mark Plus™ Labeling Software, CD-ROM.
EMPLUS-DL	Easy-Mark Plus™ Labeling Software, online download.
EMPLUS-2GO	Easy-Mark Plus™ Portable Application, USB flash drive.
EMPLUS-SERVER	Easy-Mark Plus™ Labeling Software, networkable server based version.

Windows is a registered trademark of Microsoft Corp. in the United States and/or other countries.





## **Ordering Information**



#### **Continuous Self-Laminating Labels**

- Fast-loading label cassette includes both label material and ribbon to make changing labels easy
- Self-laminating adhesive labels for wire/cable identification include a white print-on area and clear overlaminate



Self-Laminating Vinyl (VA)



**-40°C to 66°C** (-40°F to 150°F)

			inter Co	mpatibili	ty	Print-On Area	Wie	Width		gth	Prin Area	t-On Width			Wire/ Cable	Std. Pkg.	Std. Ctn.		
Part Number	Part Description	MP75	MP100	MP200	MP300	Color	ln.	mm	Ft.	m	ln.	mm	ln.	mm	ln.	mm	Size Range	Qty.	Qty.
S000X100VAM	MP Cassette, Continuous Self-Lam Tape, Vinyl, 1.0" W x 26' L White	N	Y	Y	Y	White	0.945	24	26.2	8.0	0.315	8	0.10	2.5	0.20	5.1	10 – 12 AWG	1	5



#### **Continuous Heat Shrink Labels**

- Fast-loading Label Cassette includes both label material and ribbon to make changing labels easy
- Non-adhesive flattened heat shrinkable polyolefin for wire/cable identification



Heat Shrinkable Polyolefin
3:1 Heat Shrink Ratio (H1, H2)
Heat Shrinkable Polyolefin
2:1 Heat Shrink Ratio (HP, HX)



**-40°C to 125°C** (-40°F to 257°F)

-55°C to 125°C (-67°F to 257°F)

				Pi	rinter Co	mpatibi	lity	Ribbon &	Wi	Width		Width Le		Width L		Width L		/idth Ler		ngth	Min. Cable O.D		n. Max. O.D. Cable C		Wire/ Cable		Std.
Part Number	Part Description	Shrink Ratio	Mil Spec	MP75	MP100	MP200	MP300	Material Color			Ft. m		ln.	mm	ln.	mm	Size Range		Ctn. Qty.								
H000X025H1M	MP Cassette, Continuous Heat Shrink Tubing, Mil Grade Polyolefin, .25" W x 8' L, White							Black on White	0.27	6.8			0.06	1.4	0.16	4.1	22–18										
H000X025H2M	MP Cassette, Continuous Heat Shrink Tubing, Mil Grade Polyolefin, .25" W x 8' L, Yellow	3:1		Y	Y			Black on Yellow	0.27	0.0			0.06	1.4	0.16	4.1	AWG										
H000X034H1M	MP Cassette, Continuous Heat Shrink Tubing, Mil Grade Polyolefin, .34" W x 8" L, White		Y					Black on White	0.37	9.3			0.07	07 1.9	0.22	7.6	18–12 AWG	1									
H000X034H2M	MP Cassette, Continuous Heat Shrink Tubing, Mil Grade Polyolefin, .34" W x 8' L, Yellow							Black on Yellow	0.37	9.3			0.07						5								
H000X044H1M	MP Cassette, Continuous Heat Shrink Tubing, Mil Grade Polyolefin, .44" W x 8' L, White					Y	Y	Black on White	0.40	40.0		0.5	0.00														
H000X044H2M	MP Cassette, Continuous Heat Shrink Tubing, Mil Grade Polyolefin, .44" W x 8' L, Yellow						Ť	Black on Yellow	0.48	12.3	0.2	2.5	0.09														
H000X064HPM	MP Cassette, 2:1 Continuous Heat Shrink Tubing, Polyolefin, .64" W x 8' L, White			N				Black on White	0.74	40.0			0.04	F 0	0.40	40.0	8–2										
H000X064HXM	MP Cassette, 2:1 Continuous Heat Shrink Tubing, Polyolefin, .64" W x 8' L, Yellow											Black on Yellow	0.71	18.0			0.21	5.3	0.43	10.9	AWG						
H000X084HPM	MP Cassette, 2:1 Continuous Heat Shrink Tubing, Polyolefin, .84" W x 8' L, White		N					Black on White		00.5			0.00	0.1			4–1										
H000X084HXM	MP Cassette, 2:1 Continuous Heat Shrink Tubing, Polyolefin, .84" W x 8' L,Yellow									Black on Yellow	0.87	22.5			0.32	8.1	0.54	13.7	AWG								



# **Ordering Information**



### **Continuous Tape Cassettes**

- Fast-loading label cassette includes both label material and ribbon to make changing labels easy
- Print custom pipe markers, voltage markers, signs, bin markers, and network identification labels on demand
- For flat label applications only

		F	Printer Co	mpatibili	ty	Ribbon &	Wi	dth	Ler	ngth	Std.	Std. Ctn.
Part Number	Part Description	MP75	MP100	MP200	MP300	Material Color	ln.	mm	Ft.	m	Pkg. Qty.	Qty.
T038X000VPM-BK	MP Cassette, Continuous Tape, Vinyl, 0.38" W x 23' L, Black on White.					Black on White			23	7.0		
T038X000VXM-BK	MP Cassette, Continuous Tape, Vinyl, 0.38" W x 23' L, Black on Yellow.					Black on Yellow	0.354	9.0	23	7.0		
T038X000YKM-BK	MP Cassette, Continuous Tape, Polyester, 0.38" W x 30' L, Black on Clear.					Black on Clear			30	9.1		
T050X000VPM-BK	MP Cassette, Continuous Tape, Vinyl, 0.50" W x 23' L, Black on White.					Black on White	0.472	12.0	23	7.0		
T050X000VXM-BK	MP Cassette, Continuous Tape, Vinyl, 0.50" W x 23' L, Black on Yellow.	Υ	Y			Black on Yellow						
T050X000YKM-BK	MP Cassette, Continuous Tape, Polyester, 0.50" W x 30' L, Black on Clear.			Y		Black on Clear			30	9.1		
T075X000VPM-BK	MP Cassette, Continuous Tape, Vinyl, 0.75" W x 23' L, Black on White.				Y	Black on White			23	7.0	1	5
T075X000VXM-BK	MP Cassette, Continuous Tape, Vinyl, 0.75" W x 23' L, Black on Yellow.		Ť		Ť	Black on Yellow		18.0	23			3
T075X000YKM-BK	MP Cassette, Continuous Tape, Polyester, 0.75" W x 30' L, Black on Clear.		_			Black on Clear			30	9.1		
T100X000MPM-BK	MP Cassette, Continuous Tape, Magnetic, 1.00" W x 4.9' L, Black on White.					Black on White			4.0	1.5		
T100X000MXM-BK	MP Cassette, Continuous Tape, Magnetic, 1.00" W x 4.9' L, Black on Yellow.	N				Black on Yellow		24.0	4.9	1.5		
T100X000VPM-BK	MP Cassette, Continuous Tape, Vinyl, 1.00" W x 23' L, Black on White.					Black on White	0.945		23			
T100X000VXM-BK	MP Cassette, Continuous Tape, Vinyl, 1.00" W x 23' L, Black on Yellow.					Black on Yellow			23	7.0		
T100X000YKM-BK	MP Cassette, Continuous Tape, Polyester, 1.00" W x 30' L, Black on Clear.					Black on Clear			30	9.1		

Representative offering only, visit www.panduit.com for complete listing of products.





# Mid-Range Mobile Printer Comparison









FEATURES	MP200	BMP21-PLUS	PT-E300M	Rhino 4200
Price	\$\$	\$\$	\$\$	\$\$
Label Width	1.0 in.	0.75 in.	0.7 in.	0.75 in.
Label Offering	****	****	***	***
Print Speed	1.2 lps	0.4 lps	0.8 lps	0.6 lps
Cutter	Automatic: Full and Half Cutting	Manual	Manual	Manual
Barcode, Symbols & File Storage	****	**	***	**
PC Interface and Connectivity	EasyMark Plus Labeling Software/USB	None	None	None

Competitive comparison based on published specifications.

## **PXE SERIES**









WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300

PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico cs-la@panduit.com Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information Visit us at www.panduit.com Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300