

|  | I'HIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORF | Ρ. |
|--|--|----|
|--|--|----|

| THO GOT THO THOUBED ON A                             | A NESTRICTED DASIS AND IS NOT TO BE U  |
|--|--|
| Material   | High Conductivity<br>Seamless Copper Tube  |
| Plating  | Electro-Tin  |
| Wire Size  | 250 kcmil  |
| Wire Type  | Stranded Copper; Class B:<br>Compact, Compressed or<br>Concentric, Class C: Concentric   |
| Wire Strip Length                                    | 1-5/16 in.   |
| Stud Size  | 3/8 in.  |
| UL Listed Wire<br>Connector                          | Yes, for applications up to 35kv.<br>Consult cable manufacturer for<br>voltage stress relief instructions<br>with applications greater than<br>2000 volts. |
| UL Temperature<br>Rating                             | 90° C  |
| C.S.A Certified<br>Wire Connector                    | N/A  |
| Panduit Color Code<br>on Barrel                      | YELLOW   |
| Panduit Die Index No.<br>on Barrel                   | P62  |
| Alternate Industry<br>Die Index No. ( )<br>on Barrel | (16)   |







|     |      |      |      |                  |        | CORP. TINLEY PARK, ILLINOIS   |
|-----|------|------|------|------------------|--------|---|
| 00  | 6/18 | JHNU | JHNU | DRAWING RELEASED | 043942 | LCDN250-38D-X Copper Lug - Narrow Tongue, Two-Hole, Standard Barrel |
| REV | DATE | BY   | СНК  | DESCRIPTION      | ECN    | SCALE N/A DRAWING NO / CAD FILE I CDN250-38D-CUST                   |