HIS COPY IS PROVIDED ON	A RESTRICTED BASIS AND IS NOT TO BE USE	D IN ANY WAY DETRIMENTA	L TO TI		ERESTS OF PANDUIT CORP.
Material	High Conductivity Seamless Copper Tube				
Plating	Electro-Tin				
Wire Size	2 AWG				.63 R Ref
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric				Color coded barrel markings
Wire Strip Length	1-1/4 in.	.75±.04	_	2 STR CU	
Stud Size	1/2 in.			2 ST	
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.63±.04		1.75±.	0253±.02 DIA (2) PLS
UL Temperature Rating	90° C	I			
C.S.A Certified Wire Connector	Yes				
Panduit Color Code on Barrel	BROWN				
Panduit Die Index No. on Barrel	P33				- 1.16±.04 - Beveled wire
Alternate Industry Die Index No. () on Barrel	(10)	v	Vire in	spect	ion window
CERTIFIED LISTED Wire Connector					
					CORP. TINLEY PARK, ILLINOIS
					LCC2-12W-Q
)1 8/12 JHNU JHNU		N10883TS-LCC2-12W-CUST			Copper Lug - Two-Hole, Long Barrel with Window SCALE N/A DRAWING NO/CAD FILE ICC2-12W-CUST
EV DATE BY CHK	DESCRIPTION	ECN	-R	205	N/A DRAWING NO / CAD FILE LCC2-12W-CUST