


## THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

THE COLL TO TROVIDED CITY	THE STRICTED BASIS AND IS NOT TO BE USE			
Material	High Conductivity Seamless Copper Tube Electro-Tin			
Plating				
Wire Size	2 AWG			
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric			
Wire Strip Length	1-1/4 in.			
Stud Size	1/2 in.			
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.			
UL Temperature Rating	90° C			
C.S.A Certified Wire Connector	Yes			
Panduit Color Code on Barrel	BROWN			
Panduit Die Index No. on Barrel	P33			
Alternate Industry Die Index No. ( ) on Barrel	(10)			











								CORP. TINLEY PARK, ILLINOIS
								LCB2-12WF-Q
00	4/17	JHNU	JHNU	DRAWING RELEASED	019765	RGB	RGB	Copper Lug - One-Hole, Long Barrel with Window, 90° Angle Tongue
REV	DATE	BY	СНК	DESCRIPTION	ECN	-R	SUP	SCALE DRAWING NO / CAD FILE