Material	High Conductivity Seamless Copper Tube	
Plating	Electro-Tin	
Wire Size	14 - 10 AWG STR, 12 - 10 AWG SOL	.48 R Ref
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric	
Wire Strip Length	7/16 in.	$.56\pm.04 $ $(-+-)$ $.56\pm.04 $
Stud Size	3/8 in.	
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.36±.04 - 1.00±.0241±.02 DIA (2) PLS
UL Temperature Rating	90° C	2.38±.06
C.S.A Certified Wire Connector	Yes	
Panduit Color Code on Barrel	N/A	
Panduit Die Index No. on Barrel	N/A	.38±.04 Beveled wire entry
Alternate Industry Die Index No. () on Barrel	N/A	Wire inspection window .13±.01 .22±.01
CERTIFIED	.04±. D LISTED Wire Connector	01

						CORP. TINLEY PARK, ILLINOIS
01	12/04	JHNU	JHNU	REVISED WIRE SIZE	12305	LCD10-38D-L Copper Lug - Two-Hole, Standard Barrel
REV	DATE	BY	СНК	DESCRIPTION	ECN	SCALE N/A DRAWING NO / CAD FILE LCD10-38D-CUST